

45U SmartRack 2-Post Open Frame Rack, 800 lbs (362.9 kgs) Capacity - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POST



Highlights

- 45U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes
- Toolless button keyhole mounting slots accept PDUs or cable managers

Package Includes

- SR2POST
- 28 pieces each of 12-24 screws and washers for equipment mounting
- Installation hardware
- Cable management hooks
- Warranty information
- Owner's Manual

Description

SR2POST 2-Post SmartRack Open Frame Rack is an economical way to accommodate 45U of rack space for 19-inch rack-mount applications where space is at a premium. Its heavy-duty, aluminum construction can safely support 800 pounds (362.9 kilograms) of rack-mount equipment. The black, textured powder coat finish makes it resistant to scratching while giving it a classic, attractive appearance. The SR2POST is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting holes, and bolt down provisions. Only standard hand tools are required for installation (9/16" wrench and 9/16" socket/ratchet). Multiple units can be bolted together side by side for easy expansion or customization when required. The SR2POST 2-Post SmartRack Open Frame Rack has been approved by EIA-310-D, IEC 60297-3-100, and RoHS.

Features

- Supports 800 lbs (362.9 kgs) of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Toolless button keyhole mounting slots accept PDUs and cable managers
- Easy assembly

Specifications

OVERVIEW	
UPC Code	037332127563
Device Compatibility	Patch Panel; Network Switch; UPS; Server



Powering Business Worldwide

TRIPP LITE
SERIES

Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	45U
Rack Depth	Extra Deep
EIA Mounting Rails	12-24 threaded and numbered vertical mounting rails
Mounting Holes or Slots	Yes
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Shipping Dimensions (hwd / in.)	4.90 x 6.30 x 88.00
Shipping Dimensions (hwd / cm)	12.45 x 16.00 x 223.52
Shipping Weight (lbs.)	33.00
Shipping Weight (kg)	14.97
Unit Dimensions (hwd / in.)	84.010 x 20.300 x 13.500
Unit Dimensions (hwd / cm)	213.36 x 51.56 x 12.07
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Weight Capacity - Stationary (kg)	363
Weight Capacity - Stationary (lbs.)	800
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.