

SmartRack Heavy-Duty 12U 2-Post Open Frame Rack

MODEL NUMBER: SR2POST12HD



Compact 2-post rack houses and organizes 19 in. equipment, such as servers and switches, and can be secured to any flat surface.

Features

Compact 12U 2-Post Rack Houses Equipment up to 12 in. Deep

This SmartRack® EIA-310 open frame rack is designed to house 12U of equipment, including servers, UPS systems, switches, cable managers and PDUs. It's recommended for mounting equipment in retail locations, classrooms, back offices, audio/video editing bays and radio/television studios. Constructed from heavy-duty steel with a durable black powder-coated finish, the 2-post rack has a maximum load capacity of 350 pounds (159 kilograms).

Bolts Down Almost Anywhere to Protect Equipment and Save Space

The special cantilever design allows the SR2POST12HD to house heavy equipment up to 12 inches (30.5 centimeters) deep without the risk of tipping over. Securement brackets and rubber feet are included for anchoring the rack to a flat surface with user-supplied hardware. The rack offers a small footprint and is able to fit almost anywhere in virtually any environment. You can position the open frame rack on any flat surface, including a floor, shelf or workbench.

Open Frame Design Allows Easy Access

The SR2POST12HD gives you instant access to equipment and cabling in both the front and rear. Install equipment using the 12-24 threaded and numbered mounting positions. Keyhole slots on the sides accept toolless 0U mounting of PDUs and cable managers.

Highlights

12U 2-post rack made from powder-coated steel that stands up to tough environments
Stable cantilever design allows mounting of heavy equipment without threat of tipping
Keyhole slots accept toolless 0U vertical mounting of PDUs and cable managers
Heavy-duty open frame rack allows maximum equipment load up to 350 lb.
Easy to assemble with included hardware for immediate mounting of rack equipment

Applications

Store and organize rack-mount network components up to 350 lb. on a flat surface, such as a floor, shelf or workbench

Package Includes

Base(2) Upright brackets
Support bar(2)
Securement brackets(16)
M5 x 12 mm screws(4)
Rubber feet
Installation guide

Specifications

OVERVIEW	
UPC Code	037332258540
Device Compatibility	Network Switch; PDU; Patch Panel; Server; UPS
Rack Type	Open-Frame
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Rack Height	12U
Rack Depth	Shallow
EIA Mounting Rails	12-24 threaded and numbered vertical mounting rails
Maximum Device Depth (cm)	30.48
Maximum Device Depth (in.)	12.00
Maximum Device Depth (mm)	305
Shipping Dimensions (hwd / in.)	7.87 x 27.16 x 17.52
Shipping Weight (kg)	10.21
Unit Dimensions (hwd / in.)	24.610 x 20.690 x 11.700
Unit Dimensions (hwd / cm)	62.509 x 52.553 x 29.718
Unit Weight (lbs.)	22.00
Unit Weight (kg)	9.98
Weight Capacity - Stationary (kg)	159
Weight Capacity - Stationary (lbs.)	350
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); UL 62368-1
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.