


12-Outlet Power Strip with Surge Protection, (10-15A & 2-20A), 15 ft. (4.57 m) Cord, 1650 Joules, 36 in. length

MODEL NUMBER: **SS361220**



Easily add extra surge-protected power outlets in computer rooms, equipment racks, raceways, workbenches, repair shops, labs or anywhere that needs to connect many electrical devices simultaneously to a single AC wall outlet.

Description

Need to power and surge-protect multiple pieces of equipment in close proximity to one another? The SS361220 power strip with integral AC surge protection is a convenient way to give you many surge-protected power outlets where you need them, when you need them. The SS361220 contains a 15-foot (4.6-meter) cord, 10 NEMA 5-15R outlets and two NEMA 5-15/20R outlets. Each outlet has a 2.48-inch center-to-center spacing, which is wide enough for most transformers or AC adapters. To eliminate need for a separate surge protector that can clutter up your work area, the SS361220 contains a premium-grade surge suppressor rated at 1650 joules for absorbing even the most severe high-energy AC transient surges and EMI/RFI line noise that can damage computers and other sensitive electronics. Encased in a rugged all-metal housing, the SS361220 comes with adjustable mounting clamps for vertical or horizontal mounting, making it ideal for powering multiple loads in equipment racks, computer rooms, repair shops, workbenches and raceways in a variety of internetworking, telecommunication and audio/video applications. An illuminated rocker-style power switch with a locking transparent cover prevents accidental turnoffs, while a resettable 20A circuit breaker guards against dangerous circuit overloads. To match the decor of most professional settings, it has an attractive gray housing with black receptacles.

Features

Multi-Outlet 120V Power Distribution and Surge Protection for Locations with Limited Free Space

- A 2400W, 120V, 20A, corded, multi-outlet power strip connects multiple electrical devices to a single AC wall socket
- Contains an integral surge protector to eliminate the need for a separate desktop unit that can clutter up your work space
- Saves the time and cost of installing new outlets in un-powered areas
- Ideal for branch circuit power distribution to telecommunications, computers or internetworking equipment in rack enclosures, workbenches, table tops, work stations, offices, factories, repair shops, test stands and engineering labs

12 Convenient Outlets Power All Standard Electrical Equipment

- Consists of 10 NEMA 5-15R and 2 NEMA 5-15/20R, which feature a T-shaped neutral hole to accept both 5-15P and 5-20P plugs outlets for powering equipment with up to a 20A current rating

Highlights

- 12-outlet (ten 5-15R and two 5-15/20R) power strip with a 15-ft. (4.57 m) Cord
- Rated at 2400W, 120V, 20A, featuring a resettable circuit breaker to automatically prevent circuit overloads
- Integral, premium-grade, 1650-Joule surge suppressor to protect sensitive electronics against destructive, AC transient surges and line noise
- Easy-to-install, vertical or horizontal mounting with adjustable mounting clamps
- Rocker-style, illuminated power switch with a locking safety cover to prevent accidental turn offs
- Certified to meet UL 1449 3rd Edition and UL 1363 standards

Package Includes

- SS361220 Power Strip/Surge Suppressor
- Set of adjustable mounting clips
- Warranty information
- Instruction manual



Powering Business Worldwide

TRIPP LITE
SERIES

- Each outlet is 2.48 inches apart (center to center), allowing enough room for most AC adapters and transformers
- An extra-long, 15-ft. (4.57 m) cord can reach wall outlets mounted in a different area or room from where it draws AC power, putting you in control of getting reliable power where you need it most

Premium-Grade, Surge Suppression to Protect Against Destructive Surges and Line Noise

- Contains a premium-grade surge suppressor rated at 1650 Joules that goes well beyond competing surge protectors, giving you an exceptional level of AC transient surge and EMI/RFI line noise protection for computers and other sensitive electronics

Adjustable Vertical and Horizontal Mounting Options

- Convenient method of optional horizontal or vertical power distribution
- Its 36-in. length and strip-style form factor fits in the most confined spaces unobtrusively
- Easy-to-install with adjustable mounting clamps

Premium Safety Features

- Features an illuminated, rocker-style power switch with a locking, transparent guard to prevent accidental turn offs
- An integral, 20-amp resettable circuit breaker prevents dangerous circuit overloads that can irreversibly damage connected equipment

Rugged, Durable Housing

- A rugged, all-metal housing is durably constructed making it a great solution for industrial applications
- An attractive gray housing with stylish black receptacles match the decor of most professional settings

Specifications

OVERVIEW	
UPC Code	037332186423
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P
Input Cord Details	SJT
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(10) 5-15R; (2) 5-15/20R
Circuit Breaker (amps)	20
Outlet Spacing	2.48-in. center-to-center spacing
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker and lighted 2-position power switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1650
UL1449 Let Through Rating	500V UL verified
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Power Cord Color	Black
Housing Color	Silver
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.40 x 40.00
Shipping Dimensions (hwd / cm)	6.10 x 11.18 x 101.60
Shipping Weight (lbs.)	4.85
Shipping Weight (kg)	2.20
Unit Dimensions (hwd / in.)	1.250 x 1.620 x 36.000
Unit Dimensions (hwd / cm)	3.18 x 4.11 x 91.44
Unit Weight (lbs.)	3.94
Unit Weight (kg)	1.79
Outlet Spacing	2.48-in. center-to-center spacing
Mounting Details	Set of adjustable mounting clamps



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Mounting Accessory Included	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.