

Protect It! 3-Outlet Power Cube Surge Protector - 6 USB-A Ports (7.2A Shared), 6 ft. (1.83 m) Cord, 540 Joules, Black

MODEL NUMBER: TLP366CUBEUSBB



Surge protector cube with removable USB charger safeguards your home/office electronics against surges and provides fast USB charging.

Features

Compact Cube-Shaped 3-Outlet Surge Protector with USB Safeguards Your Electronics Ideal for your home or office workstation, this Protect It!® three-outlet power cube features a surge protection rating of 540 joules to defend your sensitive electronic components against strong power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP366CUBEUSBB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). The three-inch cube is perfectly sized to fit inconspicuously into your workspace or take with you to the office, dorm, hotel or conference room.

3 NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices The power cube works as a complete unit or can be split into two, so you can leave one portion at your desk and use the other for travel. The bottom portion contains three NEMA 5-15R outlets for powering your PC, printer, wireless router, game console, television or other home/office electronics. Each outlet is located apart from the others to accommodate bulky power transformers.

6 USB-A Ports Keep Your Mobile Devices Charged to Capacity The top portion features four USB ports that share 4.8A for charging your smartphone, tablet and other USB mobile devices. The bottom portion, in addition to three NEMA 5-15R outlets (see above), has two USB ports that share 2.4A. The ability to charge up to six mobile devices at the same time makes the TLP366CUBEUSBB vital for busy families. Plus, the ability to split the power cube into two separate units means you can take one with you for instant charging on the road.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being Automatic shutoff permanently cuts power to outlets if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A green LED confirms your connected equipment is protected.

Highlights

- 3 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 540 joules protect your valuable electronics against dangerous surges and spikes
- 6 USB-A ports provide charging power for phones, tablets and other mobile devices
- 6-ft. (1.83 m) pivoting cord with right-angle NEMA 5-15P plug allows flexibility in placing the cube
- Green LED reassures you at a glance that your connected electronics are protected

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Charge smartphones, tablets or other USB devices via USB ports

Package Includes

- TLP366CUBEUSBB Protect It! 3-Outlet Surge Protector Power Cube, Black
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Use the Power Cube as One Component or Split It into Two The removable top portion with four USB ports includes a NEMA 1-15P plug, so you can take it on the road separately for charging mobile devices at school, in the airport and at the hotel. The plug folds into the unit to shield it from damage and prevent it from snagging or scratching your bag's contents. The cube's bottom portion has a 6-ft. (1.83 m) pivoting power cord and space-saving right-angle NEMA 5-15P plug, which helps you connect to a wall outlet located behind furniture placed flush against the wall.

Specifications

OVERVIEW	
UPC Code	037332238528
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
CHARGING	
Number of Charging Ports	6
Total Charging Watts	33



Powering Business Worldwide

TRIPP LITE
SERIES

Charging Method	USB
Charging Port Type	(6) USB A (FEMALE)
Charging Ports / Amps	(2) 2.4A; (4) 4.2A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	5.20 x 4.40 x 4.50
Shipping Dimensions (hwd / cm)	13.21 x 11.18 x 11.43
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Unit Dimensions (hwd / in.)	3.150 x 3.150 x 3.200
Unit Dimensions (hwd / cm)	13.21 x 6.86 x 13.46
Unit Weight (lbs.)	1.040
Unit Weight (kg)	0.47
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No



Powering Business Worldwide

TRIPP LITE
SERIES

GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); NOM (Mexico); UL 1449; UL 1363
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.