

USB-A to RJ45 Rollover Console Cable (M/M) - Cisco Compatible, 250 Kbps, 10 ft. (3.05 m), Black

MODEL NUMBER: U009-010-RJ45-X



Rollover console cable connects your computer or laptop's USB-A port to a serial-based Cisco device with a console port.

Features

Ideal for IT Pros Who Need a Connection Between Computer and Cisco Console Device This rollover cable is designed for consumers or IT professionals who want a reliable connection between their computer or laptop's USB-A port and a Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port. The cable works with both older and new Cisco models, supporting data transfer rates up to 250 Kbps.

Top-Quality Construction for Top-of-the-Line Performance No extra software or external power is required to use this 10-ft. (3.05 m) cable. Premium double shielding eliminates crosstalk and reduce EMI/RFI line noise that can disturb your electronics and inflict hardware damage or data loss. The U009-010-RJ45-X is compatible with Windows (up to 11), Mac (up to 10.12) and Linux (up to Redhat 9.0) operating systems.

Highlights

- Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem
- 10-ft. (3.05 m) cable supports data transfer speeds up to 250 Kbps
- Double-shielded construction cuts crosstalk and EMI/RFI line noise
- Plug-and-play operation with no software required for easy, immediate installation
- Compatible with Windows, Mac and Linux

Applications

- Program, reset or reboot a serial-based Cisco switch, firewall, router or modem through its console port

System Requirements

- Computer or laptop with USB-A port
- Serial-based Cisco device with console port
- Windows (up to 11), Mac (up to 10.12), or Linux (up to Redhat 9.0) operating systems

Package Includes

- U009-010-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 10-ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	03733222114
Technology	Cat5/5e; USB
Host Connector	USB A (MALE)
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (MALE)
PHYSICAL	
Color	Black
Material of Construction	PVC, PE
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	5.5mm; 4.7mm +/- 0.15
Wire Gauge (AWG)	26
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Cable Length (cm)	305
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.2866
Unit Weight (kg)	0.13
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0-90% non-condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
IP68 Rated	No
IP20 Rated	No
Suspend Mode Support	Yes
Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.