

USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), Angled Connector, White, 1 ft. (0.31 m)

MODEL NUMBER: U060-001-KPA-WH



1 ft. cable with angled connector adds a USB-A female port to a fixed location, such as a keystone wall plate or panel. Optional panel mount adapter included for installation in a motherboard, podium or kiosk.

Features

Mounts a USB 2.0 Female Port in a Fixed Location

- USB-A female keystone jack snaps easily into wall plate or panel
- Optional panel mount adapter allows installation in motherboard, podium or kiosk
- Hides components out of sight to eliminate cable clutter
- Angled female connector permits more flexible installation in tight spaces
- White in color to match most common wall plates

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded connectors with gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief helps cable and connectors move freely without stress or cracking
- Rugged PVC jacket protects twisted 28/24 AWG data/power lines
- Heavy-duty plastic housings designed for durability and long life

Specifications

OVERVIEW	
UPC Code	037332209917
Product Type	USB Keystone
Technology	USB 2.0 (High Speed)

Highlights

- Angled female connector allows more flexible installation in tight spaces
- Gold-plated contacts for max conductivity and minimum data loss
- Optional panel mount adapter secures to podium or kiosk
- Keystone design snaps easily into standard wall plate or panel
- White in color to match most common wall plates

Package Includes

- U060-001-KPA-WH USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), White, 1 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
PHYSICAL	
Color	White
Material of Construction	PVC, ABS
Cable Jacket Color	White
Connector Color	White
Cable Outer Diameter (OD)	0.15 mm
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Cable Length (cm)	30.48
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.