

Mini Bluetooth 5.0 (Class 2) USB Adapter

MODEL NUMBER: U261-001-BT5



Connects Bluetooth 5.0 wireless keyboards, mice, headsets, printers, smartphones and tablets to your computer's USB-A port.

Features

Add Bluetooth 5.0 Wireless Capability to Your Computer or Laptop

This low-profile Bluetooth 5.0 (Class 2) USB adapter connects to your PC or laptop's USB-A port to provide instant Bluetooth wireless capability. Compliant with Bluetooth 5.0 LE+EDR Class 2 standards, the U261-001-BT5 is ideal for wireless communication between your computer and up to seven Bluetooth 5.0 devices at the same time, including smartphones, tablets, keyboards, mice, headsets and printers.

Broadcasts a Wireless Signal up to 165 ft.

The USB adapter has a wireless range up to 165 feet (50 meters) and supports data transfer speeds up to 3 Mbps. Built-in security measures ensure your pairing, encryption and authentication information remains private.

Convenient Low-Profile Design Keeps You Connected as Long as You Like

This Bluetooth adapter protrudes less than 3/16 of an inch (about five millimeters) from the USB port, so it can remain connected while your laptop is inside a sleeve, briefcase or backpack. It's backward compatible with previous Bluetooth versions, so you can use the adapter to connect older devices.

Highlights

- Adds fast, reliable Bluetooth 5.0 LE+EDR Class 2 accessibility to your PC or laptop
- Supports data transfer speeds up to 3 Mbps to a wireless range up to 165 ft.
- Connects up to 7 devices simultaneously, including printers, speakers and headsets
- Backward compatible with previous Bluetooth versions, including 1.1, 1.2, 2.0, 3.0 and 4.0
- Built-in security keeps your pairing, encryption and authentication info confidential

System Requirements

- Computer with USB-A port
- Windows 8, 10 or 11 or Linux operating system

Package Includes

- U261-001-BT5 Mini Bluetooth 5.0 USB Adapter
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332272676
Technology	USB 2.0 (High Speed)
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.50



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
PHYSICAL	
Color	Black
Material of Construction	Steel, PVC
Unit Dimensions (hwd / in.)	0.240 x 0.540 x 0.740
Unit Dimensions (hwd / cm)	0.63 x 1.38 x 1.89
Unit Packaging Type	Box
Unit Weight (lbs.)	0.004
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
BTUs	1.2 BTU/Hr
Operating Humidity Range	20% to 90% RH, Non-Condensing
Storage Humidity Range	20% to 90% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	164
Signal Range (m)	50
Bluetooth Class	Class 2
Bluetooth Version	5.0
Modulation Type	GFSK (1MBPS), /4-DQPSK (2MBPS) and 8-DPSK (3MBPS)
Spread Spectrum	Frequency Hopping Spread Spectrum (FHSS)
RF Power Output	3.06dBm, GFSK
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.