

7-Port USB Charging Station with Quick Charge 3.0, USB-C Port, Device Storage, 5V 4A (60W) USB Charge Output

MODEL NUMBER: U280-007-CQC-ST



Charges and organizes up to 7 electronic devices at the same time. Storage compartment neatly organizes your excess cabling to reduce clutter when charging, and stores it out of the way when not in use. Recommended for quick-charging and storing tablets, smartphones and other mobile devices.

Description

Whether you're at home or in the office, the U280-007-CQC-ST 7-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to seven tablets, smartphones and other devices at the same time. The U280-007-CQC-ST doesn't require a computer, so you can take it anywhere AC power is available.

The U280-007-CQC-ST features five USB-A ports, each capable of delivering up to 5V 2.4A, which is enough for charging even battery-intensive devices. A USB-C port provides up to 5V 3A for more powerful devices. Plus, a Quick Charge 3.0 port is capable of rapid-charging compliant devices up to four times faster than normal USB charging.

In addition, this charging station doubles as a storage unit by providing space to neatly organize cabling while your devices charge. When not in use, cables can be stored in the compartment and kept out of the way. The included adjustable brackets accommodate the number and size of the devices being charged. To charge your USB devices, simply connect the five-foot power cord's NEMA 1-15P plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity. Also, each USB-A port complies with USB Battery Charging (BC) specification v1.2. The brackets and power supply store conveniently in the charging station when not in use.

Features

Charges Up to 7 Devices at the Same Time Recommended for charging tablets, smartphones and other devices at home or work Functions anywhere AC power is available—no computer required

Provides Plenty of Juice for Charging Quick Charge 3.0 Class A 5/9/12V technology QC 3.0-compliant devices charge up to 4x faster than conventional USB charging Delivers up to 5V, 2.4A per USB-A port—enough for charging battery-intensive devices like the Apple iPad USB-C port provides up to 5V, 3A of charging power Protects against overheating, overcurrent and overcharging Complies with USB Battery Charging (BC) specification v1.2

Efficiently Stores Your Cables / Devices Too 9 adjustable brackets provide space to neatly organize devices as they charge Convenient storage compartment lets you neatly organize your cabling while your devices charge When not in use, cables can be stored in the compartment and kept out of the way

Highlights

- 5 USB-A ports provide up to 5V, 2.4A of charging power and are USB Battery Charging (BC) specification v1.2 compliant
- USB-C port provides up to 5V, 3A of charging power
- Quick Charge 3.0 port charges up to 4x faster than normal charging
- 9 adjustable storage brackets for organizing devices
- Storage compartment neatly organizes your cabling

Package Includes

- U280-007-CQC-ST 7-Port USB Charging Station
- (9) Storage brackets
- External power supply (Input: 100–240V, 50/60 Hz, 1.5A; Output: 15V, 4A)
- C7 to NEMA 1-15P power cord, 5 ft.
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Easy to Use External dual-voltage power supply with C8 power inlet and detachable C7 to 1-15P 5 ft. cord
No computer required

Specifications

OVERVIEW	
UPC Code	037332199577
Product Type	Charging Station
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
AC Power Adapter Output Specs (V / A)	15V / 4A
AC Power Adapter Cord Length (ft.)	3
AC Power Adapter Cord Length (m)	1
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50 / 60 Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	1.5A
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 15V, 4A
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	15.6
USB Power Delivery (PD) Charging Support	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

USB Power Delivery (PD) Charging Specification	2.0
Power Consumption Detail	15.6W (Operating) 0.07W (Standby)
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	(6) USB A (FEMALE)
Side B - Connector 2	USB C (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
CHARGING	
Number of Charging Ports	7
Total Charging Amps	9.1A
Total Charging Watts	60
Charging Method	USB
Charging Method Detail	Quick Charge 3.0; 5V - 1.5A (7W)
Charging Port Type	(6) USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	USB-A: 5V/2.4A USB-A QC: 3.6V~6.5V/3A, 6.5V~9V/2A, 9V~12V/1.5A USB-C: 5V/3A
Charging Ports / Amps	(5) 2.4A; (1) 3A; (1) 3A / 2A / 1.5A
Overcharge Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / in.)	2.80 x 6.30 x 10.20
Shipping Dimensions (hwd / cm)	7.11 x 16.00 x 25.91
Shipping Weight (lbs.)	2.00
Shipping Weight (kg)	0.91
Unit Dimensions (hwd / in.)	0.866 x 6.614 x 4.882
Unit Dimensions (hwd / cm)	2.2 x 16.8 x 12.4
Unit Packaging Type	Box
Unit Weight (lbs.)	1.4
Unit Weight (kg)	0.64
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	41° to 95°F (5° to 35°C)
Storage Temperature Range	-4° to 122°F (-20° to 50°C)
Relative Humidity	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	3.0
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; FCC; GS; PSE; RoHS; TUV; UL; cUL
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.