

Wireless Charging Travel Stand - 15W Fast Charging, Qi Compatible, Apple and Samsung Compatible, Black

MODEL NUMBER: U280-Q01TST-BK



Charges your smartphone or other Qi-compatible device without connecting it to a cable.

Features

Wireless Cell Phone Charger Delivers up to 15W for Apple and Samsung Phones

Who wants to plug and unplug cords when you just want to charge your phone? The U280-Q01TST-BK makes charging more convenient by doing it wirelessly. Just place your Qi-certified smartphone (including Apple, Samsung, Google and LG) on the charging stand. That's all there is to it. This wireless charging stand even works through most protective phone cases up to 5 millimeters. **Note:** Remove any magnetic or metal attachments from your phone or case before charging.

Adjustable Stand Gives You More Flexibility Over Charging

Place your phone flat on the charging pad, or use the kickstand to charge the phone vertically while you read texts, scroll through social media and stream video. The LED flashes green to indicate the charging process is underway and changes to a solid green to let you know your phone is at 100%. **Note:** The U280-Q01TST-BK does not support magnetic charging and is only wireless charging enabled.

Compact Charging Pad Fits Comfortably on Any Counter, Table or Workspace

The portable U280-Q01TST-BK takes up very little space and fits easily on your desktop or bedside table or inside your backpack or laptop bag. An included USB cable connects the charging pad to a user-supplied 20W USB wall charger, such as the 9V 2.2A U280-W01-20C1-G (sold separately). No extra charging cables are needed. Quick Charge (QC) 2.0/3.0 adapters are recommended.

Highlights

- Charges your Apple, Google or Samsung smartphone wirelessly without a cable
- LED flashes green during charging and turns solid green to indicate device is fully charged
- Charges through phone's protective case (up to 5 mm) to avoid hassle of removing it
- Adjustable kickstand allows phone to charge vertically while scrolling or watching video
- Universally compatible with all Qi-certified smartphones and other devices

System Requirements

- Compatible with all Qi-certified smartphones, including Apple, Samsung, Google and LG
- Requires USB-C wall charger up to 20W or computer with USB-C port

Package Includes

- U280-Q01TST-BK Wireless Charging Travel Stand
- USB-A to USB-C charging cable, 1 m (3.3. ft.)
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332283290
Product Type	Wireless Charging Stand
Charging Form Factor	Pad/Stand
Charger Functions	Charge



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Phone
Technology	USB; Wireless
INPUT	
Nominal Input Voltage(s) Supported	12V DC; 5V DC; 9V DC
Input Plug Type	USB-C (FEMALE)
OUTPUT	
Output Capacity (Watts)	15
Output (Watts)	15
Overload Protection	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power/Charging LED (1x): Power On = Red (Solid); Charging = Green (Flashing); Foreign Object/Debris = Red (Flashing); Over-Temperature Trigger = Red/Green (Flashing); Under/Over Voltage = Green (Flashing) + Red (Solid)
CHARGING	
Number of Charging Ports	1
Total Charging Amps	2.22
Total Charging Watts	15
Charging Method	Wireless
Charging Method Detail	Capable of wirelessly charging a compatible smartphone at charging outputs including 15W/10W/7.5W/5W (15W Max)
Charging Port Type	WIRELESS CHARGING COIL
Magnetic Charging	No
Wireless Charging	Yes
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Jacket Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.2mm
Cable Length (ft.)	3.28
Cable Length (m)	1.00
Cable Length (in.)	39.37
Cable Length (cm)	100
Total Number of Ports	1
Unit Dimensions (hwd / in.)	5.540 x 2.830 x 0.520
Unit Dimensions (hwd / cm)	14.08 x 7.20 x 1.32
Unit Dimensions (hwd / mm)	140.8 x 72.0 x 13.2
Unit Dimensions (in.)	5.54 x 2.83 x 0.52
Unit Packaging Type	Box
Unit Weight (lbs.)	0.273
Unit Weight (kg)	0.12
ENVIRONMENTAL	
Operating Temperature Range	32° to 77°F (0° to 25°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 95%
Storage Humidity Range	0% to 95%
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Y
Quick Charge Compliant	No
Driver Required	No
LED Lights	Yes
Qi Compliant	Yes
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.