

## USB-C to 3.5 mm Headphone Jack Adapter

MODEL NUMBER: **U437-001**

Connects a microphone or stereo headphones to the USB-C or Thunderbolt 3 port on your MacBook Pro, Windows laptop or Chromebook.

### Features

#### 3.5 mm Audio Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port

This USB Type-C Stereo Audio Adapter allows you to connect a microphone, earbuds, headphones or speakers to your MacBook Pro, Windows laptop, Chromebook or other device with a USB-C or Thunderbolt 3 port. This adapter allows you to bypass a defective sound card or 3.5 mm headphone jack, as well as connect to a device that offers only USB-C ports.

#### Ready to Use Right Out of the Package

The plug-and-play audio adapter requires no software or external power. The slim cable fits easily into a pocket, purse, backpack, briefcase or laptop bag for connecting on the go. The 24-bit U437-001 converts digital high-resolution audio to analog at a 96 kHz sample rate to maintain a crisp, lively sound.

## Specifications

OVERVIEW	
UPC Code	037332269669
Technology	Stereo Audio
AUDIO	
Audio Ports	3.5MM (FEMALE)
Audio Ports Details	USB-C to 3.5mm Audio Adapter
Audio Input	USB-C
Audio Output	3.5mm
Audio Specification	DAC 96 kHz, 24-Bit
INPUT	

### Highlights

- Adds a 3.5 mm headphone/mic port to a device that comes without a stereo audio jack
- Connecting to a USB-C port lets you bypass a defective sound card or audio jack
- Slim adapter fits into a backpack or laptop bag for convenient listening anywhere
- Plug-and-play operation with no software required for speedy installation
- Compatible with Android, Windows and macOS, including iPads with USB-C port

### System Requirements

- Microphone, headphones, earbuds and/or speakers with 3.5 mm plug
- Android, Windows or macOS (including iPad with USB-C port)

### Package Includes

- U437-001 USB-C to 3.5 mm Headphone Jack Adapter
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

Built-In Cable Length (ft.)	0.66
Built-In Cable Length (m)	0.2
Built-In Cable Length (in.)	7.87
Built-In Cable Length (cm)	20
Bus Powered	Yes
Product Length (in.)	10.75
Product Length (cm.)	27.3
Product Length (ft.)	0.9
Product Length (m)	0.27
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	No
<b>CONNECTIONS</b>	
Number of Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	3.5MM (FEMALE)
Side B - Connector 2	(1) 3.5MM (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PC, ABS, TPE
Cable Jacket Color	Black
Cable Jacket Material	TPE
Cable Outer Diameter (OD)	2.5mm
Cable Length (ft.)	0.43
Cable Length (m)	0.13
Cable Length (in.)	5.12
Cable Length (cm)	1.3
Shipping Dimensions (hwd / in.)	0.25 x 4.50 x 6.75
Shipping Weight (lbs.)	0.02
Unit Dimensions (hwd / in.)	0.510 x 1.100 x 1.810
Unit Dimensions (hwd / cm)	1.3 x 2.8 x 4.6
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0
Unit Weight (kg)	0.00



Powering Business Worldwide

TRIPP LITE  
SERIES

ENVIRONMENTAL	
Operating Temperature Range	-4° to 122°F (-20° to 50°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
Relative Humidity	20 ~ 80% RH
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.