

USB-C to HDMI Adapter with USB 3.x (5Gbps) Hub Port and PD Charging, HDCP, White

MODEL NUMBER: U444-06N-HU-C



Adds HDMI, USB-A and USB-C PD ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Features

Turn Your Device's USB-C Port into a Multiport Workstation

- Ideal for transmitting audio/video to a large display, adding a USB peripheral, and powering and charging a PD Charging-compliant mobile device simultaneously
- Plug-and-play operation with no software, drivers or external power required
- About the size of a credit card for easy carrying in a pocket, purse or laptop bag

Transmit Crystal-Clear 1080p Video and Digital Audio to HDMI Display

- Compatible with USB-C or Thunderbolt 3 source devices that support USB DisplayPort Alternate Mode
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Extends video from your primary display to another
- Duplicates the same video on 2 displays
- Converts a secondary display to your primary display

Connect a USB Peripheral

- USB-A port accepts flash drives, mice, keyboards, printers and other USB peripherals
- Supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1
- Provides up to 5V/1.5A (7.5W) of fast-charging power to mobile devices

Note: Host must support USB OTG (On-the-Go)

Charge a Connected Device

- USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C/Thunderbolt 3 device
- Supports power input up to 20V 3A (60W)

Note: USB-C PD port does not support Quick Charge (QC).

Built-In Cable with Reversible USB-C Connector

- Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting audio/video
- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- PD Charging port supports power input up to 20V 3A
- Reversible USB-C plug connects in either direction
- USB-A port provides up to 5V/1.5A (7.5W) of fast charging power
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDMI port)

Package Includes

- U444-06N-HU-C USB 3.2 Gen 1 USB-C to HDMI Adapter
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332193933
Product Type	Video Adapter
Technology	HDMI; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	HDMI 1.3; HDCP 1.3
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p)
Max Supported Video Resolution	HDMI: 1920 x 1080 (1080p) @ 60Hz
Extended Mode	Yes
Mirror Mode	Yes
Max Supported Color Depth	30-bit Deep Color
HDR Support	No
3D Video Supported	No
EDID Support	No
DisplayPort Alt Mode	Yes
DATA	
Data Ports	USB A (FEMALE)
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

POWER	
Power Consumption (Watts)	1.30
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Number of Charging Ports	2
Total Charging Watts	60
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports	USB-A: 5V 1.5A (7.5W); USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	USB-A Port supports fast charging up to 5V/1.5A (7.5W)USB-C Port supports PD Charging up to 20V/3A (60W)
Charging Ports / Amps	1.5A; 3A
PHYSICAL	
Color	White
Material of Construction	PVC, ABS
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Wire Gauge (AWG)	34 / 28
Shipping Dimensions (hwd / in.)	0.79 x 4.72 x 3.94
Shipping Dimensions (hwd / cm)	2.01 x 11.99 x 10.01
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
Unit Dimensions (hwd / in.)	0.551 x 1.575 x 2.323
Unit Dimensions (hwd / cm)	1.4 x 4 x 5.9



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	4.4 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-A: 5V/1.5A (7.5W); USB-C: PD Charging 20V/3A (60W)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Multi-Resolution Support	No
Ethernet Support	No
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
HDCP Specification	1.3
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.