

Universal Reversible USB 2.0 Extension Cable (Reversible Right/Left-Angle A to A M/F), 18-in. (45.72 cm)

MODEL NUMBER: **UR024-18N-RA**



Reversible Right / Left Angle USB "A" connector plugs in any direction

Features

- 18-inch, USB 2.0 Right / Left Angle A-Male to A-Female Extension, with Universal / Reversible "A" Male connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Highlights

- Universal / Reversible A-Male plugs in any direction
- Extend distances of USB 2.0 cables with this extension cable
- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
- Gold plated contacts provide superior conductivity

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 Right / Left Angle A-Male to A-Female Extension Cable - 18-inch

Specifications

OVERVIEW	
UPC Code	037332180278
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	1.5
Cable Length (m)	0.46
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.