

## Universal Reversible USB 2.0 Cable (Reversible A to 5Pin Mini B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR030-006



Universal / Reversible "A" connector allows plugging in any direction

### Features

- Universal / Reversible "A" connector plugs in any direction
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

## Specifications

| OVERVIEW             |                         |
|----------------------|-------------------------|
| UPC Code             | 037332179531            |
| Technology           | USB 2.0 (High Speed)    |
| Cable Type           | Passive                 |
| CONNECTIONS          |                         |
| Side A - Connector 1 | REVERSIBLE USB A (MALE) |
| Side B - Connector 1 | USB MINI-B 5-PIN (MALE) |
| Connector Style      | Straight                |
| PHYSICAL             |                         |

### Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

### System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

### Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Mini-B Device Cable (A Male to 5Pin Mini-B Male)



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                              |
|-------------------------------------|------------------------------|
| Cable Jacket Color                  | Black                        |
| Cable Length (ft.)                  | 6                            |
| Cable Length (m)                    | 1.83                         |
| Shipping Dimensions (hwd / in.)     | 7.00 x 9.00 x 0.50           |
| Shipping Dimensions (hwd / cm)      | 17.78 x 22.86 x 1.27         |
| Shipping Weight (lbs.)              | 0.13                         |
| Shipping Weight (kg)                | 0.06                         |
| <b>ENVIRONMENTAL</b>                |                              |
| Operating Temperature Range         | 14° to 122°F (-10° to 50°C)  |
| Storage Temperature Range           | 5° to 140°F (-15° to 60°C)   |
| Operating Humidity Range            | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range              | 0% to 90% RH, Non-Condensing |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                              |
| Product Compliance                  | RoHS                         |
| <b>WARRANTY &amp; SUPPORT</b>       |                              |
| Product Warranty Period (Worldwide) | Lifetime limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.