



Quality Products. Service Excellence.

Heavy Duty Steel Instrument 1453 Series

Key Features:



- All steel, heavy duty construction designed to house heavy, heat producing items such as power supplies.
- Bottom of unit is 16 gauge steel, top is 18 gauge steel.
- Finished in a rugged beige powder coat.
- Top half is of an upside down “U” shape design for easy removal, bottom half is also “U” shaped but includes a fold on all sides including front & back for extra strength and mounting of top case.
- Top case section is heavily ventilated for excellent air circulation with an attractive slant (also doubles as a lifting area - both front & back).
- Top lip extends 0.75” (19 mm) on both sides adding 1.5” (38 mm) to the total depth.
- Bottom is solid except for 4 holes for mounting heavy duty rubber feet.
- Includes nickel plated self-tapping screws and screw on 0.75” (19 mm) high, rubber feet (1421T7).

Enclosures

Part Number	Height	Width	Depth
1453B	6.00	6.00	9.50
1453C	7.00	7.00	11.00
1453K	10.00	9.00	18.00
1453N	12.00	12.00	19.00

Tags: instrument, steel instrument, steel enclosure, vented

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.