



Quality Products. Service Excellence.

Painted Diecast Stomp Box Enclosures *1590-STOMP Series*

A Selection of Popular Colors & Sizes



WARNING: Many websites sell knockoffs and copies using Hammond part numbers, or "similar to Hammond." Make sure it says Hammond!

Key Features

- Rugged diecast aluminum alloy electronic instrument enclosure.
- Diecast material is tough yet easy to machine.
- Factory powder coated to save stomp box manufacturers and experimenters time and money.
- Coated with a smooth glossy polyester powder coat for a lasting finish, even after machining.
- Smooth finish allows for easy adhesion of labels or silk screens.
- Colors are matched to standard RAL colors.
- Lap joint construction provides protection against access of dust and splashing water. Also provides for improved EMI/RFI shielding.
- Designed to meet IP54. See gasket kit accessory below to meet IP65. IP65 rating also requires water-tight screws.
- Low side wall draft angle (2° or less) for easy PC board mounting.
- Unfinished and textured black versions are also available and in additional sizes and styles - See "Diecast Aluminum" and "Trapezoid and Octagon Diecast".

Replacement Hardware

- Replacement screws - nickel plated, #6-32 x 1/2" - **1590MS100** - Package of 100.
- For an even funkier look - order our black replacement screws, #6-32 x 1/2" - **1590MS50BK** - Package of 50.

Tamper-Resistant Hardware (Upgrade!)

- Tamper-resistant screws - nickel plated, #6-32 x 1/2" - **1590MS50T** - Package of 50.
- Tamper-resistant screws - black, #6-32 x 1/2" - **1590MS50TBK** - Package of 50.

Photo Features:



Hammond stomp box enclosures come in traditional sizes and shapes as well as unique trapezoid and octagon models.

Rectangular Enclosures

Part Number	Color	RAL Number	Length	Width	Height	Optional Gasket
1590ACB	Cobalt Blue	RAL 5013	93	39	31	1590AGASKET
1590AGR	Green	RAL 6024	93	39	31	1590AGASKET
1590ALG	Light Gray	RAL 7035	93	39	31	1590AGASKET
1590AOR	Orange	RAL 2009	93	39	31	1590AGASKET
1590APR	Purple	RAL 4008	93	39	31	1590AGASKET
1590ARD	Red	RAL 3011	93	39	31	1590AGASKET
1590AYL	Yellow	RAL 1021	93	39	31	1590AGASKET
1590G2CB	Cobalt Blue	RAL 5013	100	50	31	1590GGASKET
1590G2GR	Green	RAL 6024	100	50	31	1590GGASKET
1590G2LG	Light Gray	RAL 7035	100	50	31	1590GGASKET
1590G2OR	Orange	RAL 2009	100	50	31	1590GGASKET
1590G2PR	Purple	RAL 4008	100	50	31	1590GGASKET
1590G2RD	Red	RAL 3011	100	50	31	1590GGASKET
1590G2YL	Yellow	RAL 1021	100	50	31	1590GGASKET
1590BCB	Cobalt Blue	RAL 5013	112	61	31	1590BGASKET
1590BGR	Green	RAL 6024	112	61	31	1590BGASKET
1590BLG	Light Gray	RAL 7035	112	61	31	1590BGASKET
1590BOR	Orange	RAL 2009	112	61	31	1590BGASKET
1590BPR	Purple	RAL 4008	112	61	31	1590BGASKET
1590BRD	Red	RAL 3011	112	61	31	1590BGASKET
1590BYL	Yellow	RAL 1021	112	61	31	1590BGASKET
1590B2CB	Cobalt Blue	RAL 5013	112	61	38	1590BGASKET
1590B2GR	Green	RAL 6024	112	61	38	1590BGASKET
1590B2LG	Light Gray	RAL 7035	112	61	38	1590BGASKET
1590B2OR	Orange	RAL 2009	112	61	38	1590BGASKET
1590B2PR	Purple	RAL 4008	112	61	38	1590BGASKET

Part Number	Color	RAL Number	Length	Width	Height	Optional Gasket
1590B2RD	Red	RAL 3011	112	61	38	1590BGASKET
1590B2YL	Yellow	RAL 1021	112	61	38	1590BGASKET
1590BSCB	Cobalt Blue	RAL 5013	112	61	38	1590BGASKET
1590BSGR	Green	RAL 6024	112	61	38	1590BGASKET
1590BSLG	Light Gray	RAL 7035	112	61	38	1590BGASKET
1590BSOR	Orange	RAL 2009	112	61	38	1590BGASKET
1590BSPR	Purple	RAL 4008	112	61	38	1590BGASKET
1590BSRD	Red	RAL 3011	112	61	38	1590BGASKET
1590BSYL	Yellow	RAL 1021	112	61	38	1590BGASKET
1590B3CB	Cobalt Blue	RAL 5013	116	77	38	1590B3GASKET
1590B3GR	Green	RAL 6024	116	77	38	1590B3GASKET
1590B3LG	Light Gray	RAL 7035	116	77	38	1590B3GASKET
1590B3OR	Orange	RAL 2009	116	77	38	1590B3GASKET
1590B3PR	Purple	RAL 4008	116	77	38	1590B3GASKET
1590B3RD	Red	RAL 3011	116	77	38	1590B3GASKET
1590B3YL	Yellow	RAL 1021	116	77	38	1590B3GASKET
1590BBCB	Cobalt Blue	RAL 5013	120	94	34	1590BBGASKET
1590BBGR	Green	RAL 6024	120	94	34	1590BBGASKET
1590BBLG	Light Gray	RAL 7035	120	94	34	1590BBGASKET
1590BBOR	Orange	RAL 2009	120	94	34	1590BBGASKET
1590BBPR	Purple	RAL 4008	120	94	34	1590BBGASKET
1590BBRD	Red	RAL 3011	120	94	34	1590BBGASKET
1590BBYL	Yellow	RAL 1021	120	94	34	1590BBGASKET
1590BB2CB	Cobalt Blue	RAL 5013	120	94	38	1590BBGASKET
1590BB2GR	Green	RAL 6024	120	94	38	1590BBGASKET
1590BB2LG	Light Gray	RAL 7035	120	94	38	1590BBGASKET
1590BB2OR	Orange	RAL 2009	120	94	38	1590BBGASKET
1590BB2PR	Purple	RAL 4008	120	94	38	1590BBGASKET
1590BB2RD	Red	RAL 3011	120	94	38	1590BBGASKET
1590BB2YL	Yellow	RAL 1021	120	94	38	1590BBGASKET
1590BBSCB	Cobalt Blue	RAL 5013	120	94	42	1590BBGASKET
1590BBSGR	Green	RAL 6024	120	94	42	1590BBGASKET
1590BBSLG	Light Gray	RAL 7035	120	94	42	1590BBGASKET
1590BBSOR	Orange	RAL 2009	120	94	42	1590BBGASKET
1590BBSPR	Purple	RAL 4008	120	94	42	1590BBGASKET
1590BBSRD	Red	RAL 3011	120	94	42	1590BBGASKET
1590BBSYL	Yellow	RAL 1021	120	94	42	1590BBGASKET
1590XXCB	Cobalt Blue	RAL 5013	145	121	40	1590XGASKET
1590XXGR	Green	RAL 6024	145	121	40	1590XGASKET
1590XXLG	Light Gray	RAL 7035	145	121	40	1590XGASKET
1590XXOR	Orange	RAL 2009	145	121	40	1590XGASKET
1590XXPR	Purple	RAL 4008	145	121	40	1590XGASKET
1590XXRD	Red	RAL 3011	145	121	40	1590XGASKET
1590XXYL	Yellow	RAL 1021	145	121	40	1590XGASKET

Trapezoidal and Octagonal Enclosures

Part Number	Color	RAL Number	Shape	Length	Width at Small End	Width at Large End	Depth
1590TRPBCB	Cobalt Blue	RAL 5013	Narrow Trapezoid	112	62	79	39
1590TRPBGR	Green	RAL 6024	Narrow Trapezoid	112	62	79	39
1590TRPBLG	Light Gray	RAL 7035	Narrow Trapezoid	112	62	79	39
1590TRPBOR	Orange	RAL 2009	Narrow Trapezoid	112	62	79	39
1590TRPBPR	Purple	RAL 4008	Narrow Trapezoid	112	62	79	39
1590TRPBRD	Red	RAL 3011	Narrow Trapezoid	112	62	79	39
1590TRPBYL	Yellow	RAL 1021	Narrow Trapezoid	112	62	79	39
1590TRPCCB	Cobalt Blue	RAL 5013	Wide Trapezoid	95	122	151	39

Part Number	Color	RAL Number	Shape	Length	Width at Small End	Width at Large End	Depth
1590TRPCGR	Green	RAL 6024	Wide Trapezoid	95	122	151	39
1590TRPCLG	Light Gray	RAL 7035	Wide Trapezoid	95	122	151	39
1590TRPCOR	Orange	RAL 2009	Wide Trapezoid	95	122	151	39
1590TRPCPR	Purple	RAL 4008	Wide Trapezoid	95	122	151	39
1590TRPCRD	Red	RAL 3011	Wide Trapezoid	95	122	151	39
1590TRPCYL	Yellow	RAL 1021	Wide Trapezoid	95	122	151	39
1590STPCCB	Cobalt Blue	RAL 5013	Octagon	133	57	133	39
1590STPCGR	Green	RAL 6024	Octagon	133	57	133	39
1590STPCLG	Light Gray	RAL 7035	Octagon	133	57	133	39
1590STPCOR	Orange	RAL 2009	Octagon	133	57	133	39
1590STPCPR	Purple	RAL 4008	Octagon	133	57	133	39
1590STPCRD	Red	RAL 3011	Octagon	133	57	133	39
1590STPCYL	Yellow	RAL 1021	Octagon	133	57	133	39

Tags: diecast, aluminum, stomp box, screw down lid, pedal box, painted, trapezoid, octagon, colorful *Data subject to change without notice*