



Quality Products. Service Excellence.

Outdoor FilterFans 3RFF Series

Type 3R

NEW



Features

- Designed for outdoor weather where resistance against falling rain, ice formation, and UV degradation is important to ensure operation of apparatus inside enclosure.
- Maintains a UL Tested NEMA Type 3R seal against enclosure without need of a rainhood
- Patented "Click & Fit" design provides a hardware-free installation.
- Plastic made from strong, heat resistant UL 94 V0 fire approved ABS material.
- Fluted filter-mat provides longer service life, holding more dust before impeding airflow extending the mean time between maintenance for outdoor enclosure, which can be especially critical for those located in remote areas.
- Offered in Light Gray (RAL 7035) and Black (RAL 9011).

Accessories

- Exhaust Filters
- Thermostats
- Replacement Filters



Part Number	Part Number	Free Flow				Exhaust Filter	
Light Gray RAL7035	Black RAL9011	Voltage	CFM	H	W	D	Light Gray RAL7035
PF22000T3RLG	PF22000T3RBK	115V AC	38	5.71	5.71	2.76	PFA20000T3RLG
PF22000T3RLG230	PF22000T3RBK230	230V AC	38	5.71	5.71	2.76	PFA20000T3RLG
PF22000T3RLG24	PF22000T3RBK24	24V DC	38	5.71	5.71	2.76	PFA20000T3RLG
PF32000T3RLG	PF32000T3RBK	115V AC	65	7.95	7.95	3.66	PFA30000T3RLG
PF32000T3RLG230	PF32000T3RBK230	230V AC	65	7.95	7.95	3.66	PFA30000T3RLG
PF32000T3RLG24	PF32000T3RBK24	24V DC	65	7.95	7.95	3.66	PFA30000T3RLG
PF42500T3RLG	PF42500T3RBK	115V AC	94	9.92	9.92	4.05	PFA40000T3RLG
PF42500T3RLG230	PF42500T3RBK230	230V AC	94	9.92	9.92	4.05	PFA40000T3RLG
PF42500T3RLG24	PF42500T3RBK24	24V DC	94	9.92	9.92	4.05	PFA40000T3RLG
PF43000T3RLG	PF43000T3RBK	115V AC	155	9.92	9.92	4.05	PFA40000T3RLG
PF43000T3RLG230	PF43000T3RBK230	230V AC	155	9.92	9.92	4.05	PFA40000T3RLG
PF43000T3RLG24	PF43000T3RBK24	24V DC	155	9.92	9.92	4.05	PFA40000T3RLG
PF65000T3RLG	PF65000T3RBK	115V AC	297	12.60	12.60	6.18	PFA60000T3RLG
PF65000T3RLG230	PF65000T3RBK230	230V AC	297	12.60	12.60	6.18	PFA60000T3RLG
PF66000T3RLG	PF66000T3RBK	115V AC	462	12.60	12.60	6.18	PFA60000T3RLG
PF66000T3RLG230	PF66000T3RBK230	230V AC	462	12.60	12.60	6.18	PFA60000T3RLG
PF66000T3RLG460	PF66000T3RBK460	460V AC	462	12.60	12.60	6.18	PFA60000T3RLG
PF67000T3RLG	PF67000T3RBK	115V AC	560	12.60	12.60	6.18	PFA60000T3RLG
PF67000T3RLG230	PF67000T3RBK230	230V AC	560	12.60	12.60	6.18	PFA60000T3RLG

Part Number		Part Number		Free Flow			Exhaust Filter		Exhaust Filter
Light Gray RAL7035		Black RAL9011		Voltage	CFM	H	W	D	Light Gray RAL7035
PF67000T3RLG460		PF67000T3RBK460		460V AC	560	12.60	12.60	6.18	PFA60000T3RLG
									PFA60000T3RBK

Tags: **Type 3R**, **filterfan**, **fan**, **filter**, **UV**, **outdoor**, **rain**, **ice**

Data subject to change without notice