




Quality Products. Service Excellence.

Adjustable Server Rack Shelf *ADS Series*

Load rated up to 550 lbs (250 kg)

TOP SELLER



Features

- Constructed of 14-Gauge Steel.
- Fits within a single EIA-310-E rack unit and telescopes to cover the entire depth.
- Available in either solid or vented.
- Can be installed in either standard tray-down or inverted (flipped) position, offering versatility for varying equipment heights, airflow needs, or clearance requirements. If your load is dynamic or segmented (like batteries), we suggest installing the **ADSB** to add more stability.
- Ships fully assembled.
- Mounts to 4 post frame/rack
- Up to 550 lbs (250 kg) **load rating** when optional **ADSB** support bar is installed.
 - Up to 330 lbs (150 kg) without ADSB installed.
- Finished in RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America.



Improved packaging better protects against shipping damage.

Gallery



Accessories

- Hardware for Rack Mounting Solutions
- Rack Equipment Installation Tool
- Rack Rail Reducer Panel



Part No. Solid	Part No. Vented	Overall Dimensions		Adjustable Depth Range		Rack Units	Weight Load Capacity	Optional Heavy Duty Support Bar
		Height	Width	Min	Max			
ADSU1825BK	ADSV1825BK	1.72	19.00	18.00	25.00	1U	350 lbs (158 kg)	ADSB
ADSU2536BK	ADSV2536BK	1.72	19.00	25.00	36.00	1U	350 lbs (158 kg)	ADSB
ADSU3642BK	ADSV3642BK	1.72	19.00	36.00	42.00	1U	275 lbs (125 kg)	ADSB

Tags: cabinet rack shelf

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.