



Quality Products. Service Excellence.

C4 Doors C4DF Series

Exclusively for use with the C4 Cabinet Series

NEW SIZES



Features

- Constructed in 16-gauge steel.
- Easily installs into **C4 Series** cabinets using integrated spring pin at top and bottom of the door.
- Hinged on left, swings from right to left.
 - Need hinging on right? Order the **C4RHINGE**.
- Includes formed plastic handle, quarter-turn lock and hinges to mount on the cabinet.
- Available in Solid, Louvered, Perforated, **acrylic window** options.
- Finished in textured RAL9005 black powder paint coat.
 - Complies with the Greenguard guidelines for indoor air quality
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.

Accessories

- Cabinet Door Replacement Lock
- Split Door Retrofit Kit

Flush with Frame with Locking Quarter Turn

Part No. Solid	Part No. Window	Part No. Vented	Part No. Vented Split (Barn)	Use with Cabinet	
				Rack Units	Width
C4DF2442SBK1	C4DF2442PBK1	C4DF2442VBK1	C4BD2442VBK1	24U	24.00
C4DF2473SBK1	C4DF2473PBK1	C4DF2473VBK1	C4BD2473VBK1	42U	24.00
C4DF2477SBK1	C4DF2477PBK1	C4DF2477VBK1	C4BD2477VBK1	44U	24.00
C4DF3077SBK1	C4DF3077PBK1	C4DF3077VBK1	C4BD3077VBK1	44U	30.00

*Perforated doors for both front and back of the cabinet are suggested for most server applications.

Surface Door with Locking Swinghandle

Part No. Solid	Part No. Window	Part No. Vented	Part No. Vented Split (Barn)	Use with Cabinet	
				Rack Units	Width
C4D2442SBK1	C4D2442WBK1	C4D2442VBK1	C4D2442BBK1	24U	24.00
C4D2473SBK1	C4D2473WBK1	C4D2473VBK1	C4D2473BBK1	42U	24.00
C4D2477SBK1	C4D2477WBK1	C4D2477VBK1	C4D2477BBK1	44U	24.00
C4D3077SBK1	C4D3077WBK1	C4D3077VBK1	C4D3077BBK1	44U	30.00

Data subject to change without notice

