



*Quality Products. Service Excellence.*

## Type 1 Mild Steel Junction Box *CHKO Series*

Hinge Door with Quarter Turn and w/ Knockouts



### Application

- Designed for general purpose indoor commercial use as a junction, pull or switch box.
- Hinged cover with latch provides easy access during installation and maintenance.

### Standards

- UL-50 Type 1
- CSA Type 1
- Complies with
  - NEMA Type 1
  - IEC 60529, IP20

### Construction

- Formed and spot welded from 16 gauge (up to 30"x24") or 14 gauge (36"x24") steel.
- Formed steel covers close by use of slotted quarter turn latch.
- Full swing, hinged door. NOTE: Former butt hinge being transitioned to new integral design starting late 2020. See image gallery for view of new hinge.
- Easily removed knockouts on all 4 sides (see drawings for sizes and locations).
- Through holes in back for wall mounting.
- Grounding location embossed in body.

### Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

### Accessories

- Type 1 Lock Kit
- CS Perforated Panels

**New and improved PDF part drawing files with more detail now available.**

Click part number in table below to access PDF, DXF, and STEP files.

| Part No.  | Enclosure |       |      |
|-----------|-----------|-------|------|
|           | H         | W     | D    |
| CHKO663   | 6.00      | 6.00  | 3.50 |
| CHKO644   | 6.00      | 4.00  | 4.00 |
| CHKO664   | 6.00      | 6.00  | 4.00 |
| CHKO864   | 8.00      | 6.00  | 4.00 |
| CHKO884   | 8.00      | 8.00  | 4.00 |
| CHKO1084  | 10.00     | 8.00  | 4.00 |
| CHKO10104 | 10.00     | 10.00 | 4.00 |

| Part No.  | Enclosure |       |      |
|-----------|-----------|-------|------|
|           | H         | W     | D    |
| CHKO1284  | 12.00     | 8.00  | 4.00 |
| CHKO12104 | 12.00     | 10.00 | 4.00 |
| CHKO12124 | 12.00     | 12.00 | 4.00 |
| CHKO16124 | 16.00     | 12.00 | 4.00 |
| CHKO18124 | 18.00     | 12.00 | 4.00 |
| CHKO666   | 6.00      | 6.00  | 6.00 |
| CHKO886   | 8.00      | 8.00  | 6.00 |
| CHKO1086  | 10.00     | 8.00  | 6.00 |
| CHKO10106 | 10.00     | 10.00 | 6.00 |
| CHKO12106 | 12.00     | 10.00 | 6.00 |
| CHKO12126 | 12.00     | 12.00 | 6.00 |
| CHKO16126 | 16.00     | 12.00 | 6.00 |
| CHKO16166 | 16.00     | 16.00 | 6.00 |
| CHKO18126 | 18.00     | 12.00 | 6.00 |
| CHKO18186 | 18.00     | 18.00 | 6.00 |
| CHKO24186 | 24.00     | 18.00 | 6.00 |
| CHKO24246 | 24.00     | 24.00 | 6.00 |
| CHKO30246 | 30.00     | 24.00 | 6.00 |
| CHKO36246 | 36.00     | 24.00 | 6.00 |
| CHKO36248 | 36.00     | 24.00 | 8.00 |

Tags: **CHKO, commercial, junction box, knockouts, wallmount, type 1, NEMA 1, steel, keyhole slot, hinge door, quarter turn**

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.