



Quality Products. Service Excellence.

Cable Ladder Rack *CL Series*

NEW SIZES



For high-capacity cable management in data centers, telecom rooms, and other densely wired environments, the Hammond Cable Ladder (CL Series) delivers strength, reliability, and flexibility. Designed to integrate seamlessly with Hammond rack mounting products, the CL Series can also be mounted to most standard tube-steel ladder systems and existing racks or cabinets, making it a versatile solution for both new installations and retrofit projects.

Features

- Manufactured using 16 gauge 1.50in x 0.38in USA manufactured tube steel for the ladder tray.
- Both horizontal and vertical mounting is possible with the add-on accessories listed below.
- Mounting hardware is sold separately.
- Offered in 6", 12", 18", 24" standard widths.
- Rung spaced at 12". (9" spacing available by special order.)
- Bonding holes (0.219" Ø) 3" from end of ladder.
- RAL9005 black powder paint coat. Complies with the Greenguard guidelines for indoor air quality.
- Packaged in cardboard with wood at the ends to prevent shipping damage.
- Load rated to 130 lbs (59 kg) per 10ft (3.0m) when supported every 5ft (1.5m).
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

- Universal Cable Ladder Triangle Wall Supports
- Ladder Rack Vertical Elbows
- Ladder Tray End Caps
- Ladder Wall Angle Support
- Ladder Rack Adapter Kit
- Ladder Wall Mount Bracket
- Ladder Cable Radius Waterfall
- Bolt Down Kit
- Ladder Rack Horizontal Elbows
- Butt Splice Kit
- Ladder Junction Splice Kit
- Ladder Rack Elevation Kit
- Ladder Floor Mount Bracket
- Ceiling Mount Bracket
- Bonding Wire Kits

10ft Ladder

Part No. RAL9005 Black	Part No. RAL7035 Light Gray	Ladder Pieces	Overall Dimenitons		
			Height	Width	Length
CL6W10LBK	CL6W10LLG	1	1.50	6.00	119.50
CL12W10LBK	CL12W10LLG	1	1.50	12.00	119.50
CL18W10LBK	CL18W10LLG	1	1.50	18.00	119.50
CL1810BK	-	2	1.50	18.00	119.50
CL24W10LBK	CL24W10LLG	1	1.50	24.00	119.50

White is available to order, just replace LG with WH.

10ft Ladder Quick Ship Kit

Part No.	Butt Splice Kit	Included Components		Ladder Dimensions		
		Ladder Length	Ladder Pieces	Height	Width	Total Length
CL610SKBK	1	59.50	2	1.50	6.00	119.00
CL1210SKBK	1	59.50	2	1.50	12.00	119.00
CL1810SKBK	1	59.50	2	1.50	18.00	119.00

5ft Ladder Rack-to-Wall Kit

Part No.	J-Bolt Hardware	Included Components		Ladder Dimensions		
		Wall Angle	Rack Adapter	Height	Width	Length
CL65RWKBK	Yes	Yes	Yes	1.50	6.00	59.50
CL125RWKBK	Yes	Yes	Yes	1.50	12.00	59.50
CL185RWKBK	Yes	Yes	Yes	1.50	18.00	59.50

90-Degree Horizontal Elbow

Part No.	Description	Ladder Width	Height	Width	Depth
CLEH12BK	90 Degree Corner Horizontal Elbow	12.00	1.50	29.19	29.19
CLEH18BK	90 Degree Corner Horizontal Elbow	18.00	1.50	35.19	35.19
CLEH24BK	90 Degree Corner Horizontal Elbow	24.00	1.50	41.19	41.19

90-Degree Vertical Elbow

Part No.	Description	Ladder Width	Height	Width
CLEV6BK	90 Degree Corner Vertical Elbow	6.00	13.50	13.50
CLEV12BK	90 Degree Corner Vertical Elbow	12.00	13.50	13.50
CLEV18BK	90 Degree Corner Vertical Elbow	18.00	13.50	13.50
CLEV24BK	90 Degree Corner Vertical Elbow	24.00	13.50	13.50

Cable Ladder Joining Kits & Hardware

Part No.	Description	Qty Included
CLBSK	Butt Splice Kit	One (1) Pair
CLJSK	Junction Splice Kit (T-Junction) Zinc Finish	One (1) Pair
CLJSKBK	Junction Splice Kit (T-Junction) Black Finish	One (1) Pair
CLJBK	J-Bolt Kit	One (1) Pair
C4K-Z4	Floor Lagging Kit	Four (4)
BWK6A7	#6 AWG Bonding Wire Kit	One (1) Cable

Cable Management Waterfall

Part No.	Description	Height	Width	Depth	Bend Radius
CLECR	Edge of stringer cable radius	2.45	10.00	3.63	2.00
CLE6CR	Inside rung cable radius	2.25	5.55	4.63	2.00

Universal Cable Ladder Triangle Wall Supports

Part No.	Description	Overall Dimensions		
		Height	Width	Depth
CLWS6	Support triangle for 6in wide ladder.	10.00	1.50	6.00
CLWS12	Support triangle for 12in or two (2) 6in wide ladder.	16.00	1.50	12.00
CLWS18	Support triangle for 18in or one (1) 12in and one (1) 6in wide ladder.	22.00	1.50	18.00
CLWS24	Support triangle for 24in or one (1) 12in and one (1) 6in wide ladder.	28.00	1.50	24.00

Wall mounting hardware sold separately. Includes pair of j-bolts.

Elevation Kit

Part No.	Maximum Ladder Qty	First Level		Second Level		Third Level		Overall Height
		Min	Max	Min	Max	Min	Max	
CLEK0BK	1	2.00	6.00	n/a	n/a	n/a	n/a	7.50
CLEK1BK	1	2.00	12.00	n/a	n/a	n/a	n/a	13.50
CLEK2BK	2	2.00	12.00	14.00	24.00	n/a	n/a	25.50
CLEK3BK	3	2.00	12.00	14.00	24.00	26.00	36.00	37.50

Universal Cable Ladder Accessories

Part No.	Description	Qty Included
CLWMB	Wall mount bracket for ladder tray	One (1) Pair (Wall mounting hardware not included)
CLFMB	Floor mount bracket for ladder tray	One (1) Pair (Floor lagging hardware not included)
CLCMB	Ceiling mount bracket for ladder tray	One (1) Pair (Threaded rod not included)
CLRAP	2-Post/4-Post Rack Ladder Adaptor Kit	One (1) Rack Adapter, Two (2) J-Bolts
CLRAP24	2-Post/4-Post Rack Ladder Adaptor Kit for 24in Ladder	One (1) Rack Adapter, Two (2) J-Bolts
CLWA	Wall Angle for up to 18in wide ladder with pair of J-Bolts	One (1) Angle, Two (2) J-Bolts
CLWA24	Wall Angle for up to 24in wide ladder with pair of J-Bolts	One (1) Angle, Two (2) J-Bolts
CLEP	End plugs for ladder tray	Two (2) Plastic Plugs

Surface mounting hardware sold separately.

Tags: Cable Pathway, Basket Tray, Cable Runway

Data subject to change without notice