



Quality Products. Service Excellence.

Ladder Rack Horizontal Elbows *CLEH Series*

NEW

Features



- Manufactured using 16 gauge 1.50in x 0.38in USA manufactured tube steel.
- Mounting hardware is sold separately.
- Offered in 12", 18", and 24" standard widths.
  - 6" width available by special order.
- Supports minimum bend radius cable runs with a gradual bend around a 90-degree corner.
- Maximum rung spaced at 9.7".
- Bonding holes (0.219" Ø) 3" from end of ladder.
- Textured RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
  - White and Gray powder coat is available by special order.
- Maintains load rating when used with **CLBSK**.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Butt Splice Kit
- Ladder Junction Splice Kit
- Ceiling Mount Bracket
- Universal Cable Ladder Triangle Wall Supports
- Ladder Tray End Caps
- Bonding Wire Kits

Part No.	Description	Ladder Width	Height	Width	Depth
CLEH12BK	90 Degree Corner Horizontal Elbow	12.00	1.50	29.19	29.19
CLEH18BK	90 Degree Corner Horizontal Elbow	18.00	1.50	35.19	35.19
CLEH24BK	90 Degree Corner Horizontal Elbow	24.00	1.50	41.19	41.19

Tags: Flat Turn, Cable Runway E-Bend, Horizontal E-Bend Section, 90-Degree, Cable Runway Horizontal 90°

Data subject to change without notice