



Quality Products. Service Excellence.

Rack Cabinet *DC100 Series*

Note: This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **H1 Series**. For alternative solution assistance, **contact Hammond here** or call: USA (716) 630-7030, Canada and International (519) 822-2960.



Features

- Constructed in 14-gauge steel.
- Two pairs of 19" EIA compliant square hole punched rails with rack unit markings.
- Available in two heights: 42U & 24U models
- Front and rear doors have an attractive 2 point latch, curved and ribbed surface for added stability, and can be easily removed and hinged in either direction.
- Vented doors provide 79% airflow.
- 42U Cabinet is designed for ganging multiple cabinets together without side panels. **Side panels sold separately.**
- 24U Cabinet is designed for standalone applications and comes with two side panels.
- Open bottom to allow raised tile floor cable and air access.
- Removable rear panel for floor-level cable entry.

Specifications

- Two (2) 4" diameter cable entry holes and one (1) 8" x 12" opening on top.
- Open frame bottom allows raised tile floor cable and air access.
- Frame includes four (4) leveling feet and (4) recessed casters.
- Rails are infinitely adjustable in depth.
- Grounding studs on frame, side panels, top and doors
- Finished in textured black powder paint. Also available in textured white upon request.
- UL Listed 2416 rated for up to 3,000 lbs (1,360 kg) static load rating.
- RoHS Compliant.
- Manufactured in North America.



DC100

Part No.	Overall Dimensions			Rack Units	Mounting Depth			Replaced by Part No.
	Height	Width	Depth		Height	Width	Depth	
DC1004224	49.10	24.00	45.81	24U	42.00	19.00	38.69	RB-DC2442
DC1004242	80.68	24.00	45.81	42U	73.50	19.00	38.69	H12442U42BK

Overall height includes leveling feet and casters.

DC100 Specific Accessories

Part No.	Description
DC100SP4242	DC100 42U Locking Side Panel Kit (includes 2 x panels)
DC10042RAIL	EXTRA pair of square-hole, vertical mounting rails 42U high
DC10024RAIL	EXTRA pair of square-hole, vertical mounting rails 24U high
DC100AD42	DC100 42U Air Dam Kit
DC100AD24	DC100 24U Air Dam Kit

Part No.	Description
DC100RHINGE	DC100 Right Hand Door Hinge
DC100ATIP	DC100 Stabilizer / Anti-tip Bracket

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.