



*Quality Products. Service Excellence.*

## Tube Axial Fans *DNMF Series*



### Features

- Choice of 3.15" (80mm), 4.70" (120mm), 5.91" (150mm) or 10" (254mm).
- Choice of either 115 or 230 VAC, 50/60 Hz.
- Impedance-protected motor.
- Class-B insulated.
- Ball-bearing fan construction, diecast aluminum body, and metal fan blades.
- **Note:** **FAN150AC230**, **FAN10A115**, **FAN10A220** that has plastic fan blades.
- **DNMF100AC**, **FAN150AC** and **FAN10A** fans have male plug terminations (requires fan cords).
- **FAN80AC** fans have 11" long lead wires.
- Includes mounting hardware.

### Specifications

- All fan components are recognized to UL 507
- All fan components with the exception of **FAN10A115**, **FAN10A220** and **FAN150AC115** are CSA certified to C22.2 No. 113.
- **FAN150AC115** is recognized to UL 507 and cUR recognized to C22.2 No.113, and TUV certified to EN60950-1.
- Finished in smooth black powder paint.

Save time and order our cabinet fan tops and/or fan kits:

- **Cabinet Fan Tops**
- **Fan Kits** - Come with all the essential components
- **Low-Decibel Fan Kits** - Quietly cools your equipment

### Gallery



### Accessories

- Fan Cords
- Filter Fan Grills
- Metal Fan Guard



| Part No.<br>115 VAC | Part No.<br>230 VAC | Overall Dimensions |       |       | Wattage |      |      | Speed |            | Ratings        |
|---------------------|---------------------|--------------------|-------|-------|---------|------|------|-------|------------|----------------|
|                     |                     | Height             | Width | Depth | CFM     | 50Hz | 60Hz | (RPM) | Noise (dB) |                |
| FAN80AC115          | FAN80AC230          | 3.15               | 3.15  | 1.50  | 32      | 11   | 10   | 3100  | 34         | UR, CSA, CE    |
| DNMF100AC115        | DNMF100AC230        | 4.70               | 4.70  | 1.50  | 105     | 24   | 22   | 3000  | 56         | UR, CSA, CE    |
| FAN150AC115         | -                   | 5.75               | 6.72  | 2.00  | 210     | 27   | 26   | 3100  | 63         | cURus, TUV, CE |
| -                   | FAN150AC230         | 5.90               | 6.72  | 2.20  | 230     | 46   | 40   | 3400  | 53         | UR, CSA, CE    |
| FAN10A115           | FAN10A220           | 10.00              | 10.00 | 3.50  | 550     | 30   | 35   | 1650  | 60         | cURus, CE      |

DNMF Accessories

| Part No.<br>115 VAC | Part No.<br>230 VAC | Use With Fan Guard |           | Use With Filter Grill Part No. |              |            |
|---------------------|---------------------|--------------------|-----------|--------------------------------|--------------|------------|
|                     |                     | Part No.           | Black     | Gray/Beige                     | ANSI 61 Gray | Light Gray |
| FAN80AC115          | FAN80AC230          | FAN80FG            | XPFA80BK  | XPFA80CG                       | XPFA80GY     | XPFA80LG   |
| DNMF100AC115        | DNMF100AC230        | DNFG               | XPFA120BK | XPFA120CG                      | XPFA120GY    | XPFA120LG  |
| FAN150AC115         | -                   | FAN150FG           | XPFA150BK | XPFA150CG                      | XPFA150GY    | XPFA150LG  |
| -                   | FAN150AC230         | FAN150FG           | XPFA150BK | XPFA150CG                      | XPFA150GY    | XPFA150LG  |
| FAN10A115           | FAN10A220           | FAN10FG            | XPFA254BK | XPFA254CG                      | XPFA254GY    | XPFA254LG  |

Data subject to change without notice