



Quality Products. Service Excellence.

Aluminum Rack Panels PBPA Series

Features:



- Constructed of 8-gauge (0.125") 5052-H32 Aluminum.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat or unfinished. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.



 Please be advised that the RAL9005 Semi-Gloss Black will be phased out effective January 3, 2025. The replacement is the RAL9005 Matte Black.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel



Part No.	Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height		Qty of
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Part No.	Rack	Panel	Mounting
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matte White	Unfinished	Units	Height	Points
PBPA19001BK2	PBPA19001BK	PBPA19001GY2	PBPA19001LG2	PBPA19001WH	PBPA19001UNF	1U	1.75	4
PBPA19003BK2	PBPA19003BK	PBPA19003GY2	PBPA19003LG2	PBPA19003WH	PBPA19003UNF	2U	3.50	4
PBPA19005BK2	PBPA19005BK	PBPA19005GY2	PBPA19005LG2	PBPA19005WH	PBPA19005UNF	3U	5.25	4
PBPA19007BK2	PBPA19007BK	PBPA19007GY2	PBPA19007LG2	PBPA19007WH	PBPA19007UNF	4U	7.00	4
PBPA19008BK2	PBPA19008BK	PBPA19008GY2	PBPA19008LG2	PBPA19008WH	PBPA19008UNF	5U	8.75	4
PBPA19010BK2	PBPA19010BK	PBPA19010GY2	PBPA19010LG2	PBPA19010WH	PBPA19010UNF	6U	10.50	8
PBPA19012BK2	PBPA19012BK	PBPA19012GY2	PBPA19012LG2	PBPA19012WH	PBPA19012UNF	7U	12.25	8
PBPA19014BK2	PBPA19014BK	PBPA19014GY2	PBPA19014LG2	PBPA19014WH	PBPA19014UNF	8U	14.00	8
PBPA19015BK2	PBPA19015BK	PBPA19015GY2	PBPA19015LG2	PBPA19015WH	PBPA19015UNF	9U	15.75	8
PBPA19017BK2	PBPA19017BK	PBPA19017GY2	PBPA19017LG2	PBPA19017WH	PBPA19017UNF	10U	17.50	8

Data subject to change without notice

