



Quality Products. Service Excellence.

Water-Tight, Modern Thick Wall Diecast Aluminum *R196 Series* aluPLUS

Key Features:

- Modern, high quality instrument enclosure
- Material - Aluminum die-cast: GD SI 12 / DIN 1725
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket standard. (-50°C up to +140°C)
- Dark grey plastic clip-on design covers - to hide mounting & lid screws (plastic - polyoxymethylene) - RAL 7016
- Complete with lid captivation devices
- Degree of protection: NEMA 4X, IP66
- UL Listed
- Textured polyester powder coat, light grey RAL 7035. (can be supplied unpainted on special order)



Photo Features (click to enlarge)



Enclosure can be installed after closing lid.



Snap in design covers hide both lid screws and installation holes.



Standoffs in the enclosure and lid for panels, P.C. boards & components.

Integrated recesses for membrane keypads.

Part Number	Length (mm)	Width (mm)	Depth With Lid (mm)
R196-100-000	100	100	82
R196-120-000	122	120	82
R196-082-000	125	84	59
R196-102-000	160	100	82
R196-161-000	160	160	90
R196-083-000	175	84	59
R196-122-000	220	120	82
R196-162-000	260	160	90

