



Quality Products. Service Excellence.

Luran Water-Tight Enclosures *R290 Series*

technoPLUS

Key Features:

- Premium UV-resistant Luran plastic enclosures for outdoor applications
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket included, rated -50°C up to +140°C (-58°F to 284°F)
- Degree of protection: NEMA 4X, IP 66
- Enclosure is light grey (RAL 7035) Luran with UL 94HB flammability rating
- Clip-on design covers made of plastic polypropylene (PP) in anthracite grey (RAL 7016)



Features:



Snap in design covers hide both lid screws and installation holes.



Integrated recesses for membrane keypads.



Enclosure can be installed after closing lid.



Standoffs in the enclosure and lid for panels, PC boards, and components.

Part Number	Length (mm)	Width (mm)	Height (mm)
R290-090-000	130	90	70
R290-112-000	160	110	70
R290-092-000	180	90	70
R290-132-000	230	130	90
R290-172-000	270	170	90

