



Quality Products. Service Excellence.

Server Rack Cable Manager *RB-VCM Series*

TOP SELLER



Vertical cable managers facilitate cable organization for a single or multiple rack installation. The RB-VCM is cost-effective and includes a number of unique features to save you installation time.

Features

- Manager body and door are constructed of 16-gauge steel.
- All-steel construction with side and rear cut-outs for cable pass-through.
- Includes cable mounting lances for hook and loop cable organization.
- Mounts to either side of the open-frame rack (includes mounting hardware).
- The attached hinged door opens to one side and secures closed with two (2) small strips of the magnet.
- Horizontal stabilizers easily swing away for cable installation and swing back for structural support.
- Separated space easily allows for cables to be added or removed without fishing the cable.
- Designed for use with the **RB-2P** and is also compatible with **DNRRHDW**, **DC4R**, **DRZ4**, **RB-2PA** as well as several of our competitor's open racks.
 - Hardware included for securing to rack.
- Manager and door finished in textured RAL9005 black powder paint finish.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.

RACK BASICS®

A HAMMOND BRAND



Part of the Rack Basics® line of economy rack solutions.

Accessories

- Vertical Cable Manager Extensions
- Hook and Loop Convenience Roll



Part No.	Overall Dimensions (Inches)			Mounting Dimensions		Door Included
	Height	Width	Depth	Units	Rack Units	
RB-VCM24	47.00	6.00	5.00	42.00	24	Yes
RB-VCM36	68.00	6.00	5.00	63.00	36	Yes
RB-VCM40	75.00	6.00	5.00	70.00	40	Yes
RB-VCM44	82.00	6.00	5.00	77.00	44	Yes
RB-VCM48	89.00	6.00	5.00	85.00	48	Yes

Estimated Cable Fill Capacities

Part No.	Description	Opening Quantity	Recommended Cable Fill (50% Fill Ratio)		Maximum Cable Fill (100% Fill Ratio)	
			Cat 6	Cat 6a	Cat 6	Cat 6a
RB-VCM44	Channel Opening	1	149	103	297	207
	Side Opening	2 x 19 = 38	31	21	61	42
	Rear Pass Through	10	28	19	55	38
RB-VCM48	Channel Opening	1	149	103	297	207
	Side Opening	2 x 21 = 42	31	21	61	42
	Rear Pass Through	11	28	19	55	38

Cable Manager > Hammond Rack Compatability

Part No.	RB-2P	RB-2PA19	RB-2PA23	DNRR (19")	DNRR (23")	DC2R	DC4R	DRZ4
RB-VCM24	RB-2P24	-	-	-	-	-	DC4R24	-
RB-VCM36	-	-	-	DNRR63HDW	-	-	-	-
RB-VCM40	-	-	-	DNRR70HDW	-	-	-	-
RB-VCM44	RB-2P77	RB-2PA1945BK	RB-2PA2345BK	DNRR77HDW	DNRR2377HDWB	DC2R44	DC4R44	DRZ477
RB-VCM48	RB-2P84	-	-	DNRR84HDW	DNRR2384HDWB	-	-	-

Tags: **Cable Duct**

Data subject to change without notice