



Quality Products. Service Excellence.

Rack Cabinet Fixed Shelf (Flanges Folded Down) RF Series

Load rated to 350 lbs (159 kg)

Features



- Constructed of heavy-duty 14 gauge steel.
- Front & rear lip folded for extra strength.
- The versatile design can be used upside down (front & rear lip become equipment retainers).
- Sides are folded up for easy hardware installation from above.
- Sides are slotted for easy adjustment with most rail depth locations.
- Includes all mounting hardware.
- 350 lbs (159 kg) **load rating**.
- Finished in textured RAL9005 black powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America.



Please note that to mount this product, you must have two (2) pairs of combination rails within your cabinet. To mount this product to a traditional equipment rack, please order the FSRA.



If used with our CPR square hole rails you will need to order CPRSA rail adaptor for each shelf ordered.

Accessories

- Fixed Shelf Rail Adapter
- Square Hole Mounting Rail Adaptor
- Hook and Loop Convenience Roll

Solid Part No.	Vented Part No.	Flange		Overall Dimensions		
		Height	Location	Height	Width	Depth
RFUS1918BK1	RFVS1918BK1	0.81	Front and Rear	1.94	17.75	18.00
RFUS1921BK1	RFVS1921BK1	0.81	Front and Rear	1.94	17.75	21.00
RFUS1926BK1	RFVS1926BK1	0.81	Front and Rear	1.94	17.75	26.00
RFUS1931BK1	RFVS1931BK1	0.81	Front and Rear	1.94	17.75	31.00

Data subject to change without notice

