



Quality Products. Service Excellence.

Vertical Mounting Wall Rack VPB Series

Load rated to 135 lbs (61 kg)

This product is manufactured within North America and is Tariff-Free.



Features:

- Constructed in 14-gauge steel.
- 19" mounting EIA tapped 10-32 mounting rails.
- Horizontal or vertical equipment mounting.
- Rear cable access for cable management.
 - Side cable access is included for the 6U rack.
- Finished in RAL9005 black powder paint. Complies with the Greenguard guidelines for indoor air quality.
- Includes a package of ten (10) **SCREW1032-10** screws.
- 135 lbs (61 kg) **static load rating**.
- TAA-compliant for GSA Schedule purchases.
 - BAA/TAA-compliant documentation available upon request.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

The VPB196UBK includes cutouts to be rack-mounted to provide vertical rack mounting for deep equipment such as a server.

Gallery



Accessories

- Universal Rack Shelf
- Mounting Screw and Clip Nut Combo-Pack
- Ground Stud Kit
- Hinged Clear Security Cover
- We Manufacture PDUs and Outlet Strips

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
VPB192UBK	7.69	19.19	4.19	2U	3.50	19.00
VPB194UBK	7.69	19.19	7.69	4U	7.00	19.00
VPB196UBK	11.19	19.19	11.19	6U	10.50	19.00

6U Ships unassembled in a flat-pack.

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Wall Bracket	
10	10-32 x 0.75in Rack Mounting Screws	SCREW1032-10

Tags: **Vertical Rack Bracket, Vertical Low Profile, Vertical Rack, Hub-brackets, knock-down, knock down, vp8194ubk, vp8** *Data subject to change without notice*

© 2025. Hammond Manufacturing Ltd. All rights reserved.