

BU-20608Y, Ratchet Crimping Tool

- 3 crimp nests: 0.25 – 1.5 mm², 1.5 – 2.5 mm², 4 - 6 mm²
- Ensures uniform crimp termination regardless of user.
- Release switch if terminal or wire is inserted improperly.



Butt Splices	
AI-20315	26-24 TO 22-18 VINYL INSULATED
AM10672	26-24 TO 22-18 STEP DOWN NYAX
AM10674	26-24 TO 22-18 STEP DOWN NYAX
AM10698	26-24 TO 22-18 STEP DOWN NYAX
BU-191540004	22-18 VINYL INSULATED
BU-191540015	16-14 VINYL INSULATED
BU-191540022	16-14 TO 22-18 VINYL INSULATED
BU-191540028	12-10 VINYL INSULATED
BU-191540035	12-10 TO 16-14 VINYL INSUL.
BU-192020019	16-14 NYLON ECON. BUTT CONNECT
BU-192020039	12-10 NYLON ECON BUTT CONN
BU-192020063	22-18 NYLON ECON. BUTT CONNECT

Pin Terminals	
BU-192120001	12-10 VINYL INSULATED PIN TERM
BU-192120003	22-18 VINYL INSULATED PIN
BU-192120005	16-14 VINYL INSULATED PIN TERM

Ring Terminals	
AI-50020N	22-18 NYLON INSULATED #6 RING
AI-50030N	22-18 NYLON INSULATED #8 RING
AI-50040N	22-18 NYLON INSULATED #10 RING
AI-50041N	22-18 NYLON INSULATED 1/4 RING
AI-50042N	22-18 NYLON INSULATED 5/16
AI-50043N	22-18 NYLON INSULATED 3/8 RING
AI-50086N	16-14 NYLON INSULATED #6 RING
AI-50090N	16-14 NYLON INSULATED #8 RING
AI-50100N	16-14 NYLON INSUL. #10 RING
AI-50101N	16-14 NYLON INSULATED 1/4 RING
AI-50102N	16-14 NYLON INSULATED 5/16
AI-50103N	16-14 NYLON INSULATED 3/8 RING
AI-50220N	12-10 NYLON INSULATED #8 RING
AI-50230N	12-10 NYLON INSULATED #10 RING
AI-50240N	12-10 NYLON INSULATED 1/4 RING
AI-50250N	12-10 NYLON INSULATED 5/16
AI-50260N	12-10 NYLON INSULATED 3/8 RING
BU-190540035	22-18 VINYL INSULATED #6 RING
BU-190540039	22-18 VINYL INSULATED #10 RING
BU-190540042	22-18 VINYL INSULATED 1/4 RING
BU-190540044	22-18 VINYL INSULATED 5/16
BU-190540048	22-18 VINYL INSULATED 3/8 RING
BU-190540054	22-18 VINYL INSULATED #8 RING
BU-190540075	16-14 VINYL INSULATED 3/8 RING
BU-190540086	16-14 VINYL INSULATED 1/4 RING
BU-190540088	16-14 VINYL INSULATED 5/16
BU-190540108	16-14 VINYL INSULATED #6 RING
BU-190540110	16-14 VINYL INSULATED #8 RING
BU-190540113	16-14 VINYL INSULATED #10 RING
BU-190700121	12-10 VINYL INSULATED #8 RING
BU-190700123	12-10 VINYL INSULATED #10 RING
BU-190700132	12-10 VINYL INSULATED 1/4 RING
BU-190700136	12-10 VINYL INSULATED 5/16
BU-190700153	12-10 VINYL INSULATED 3/8 RING
HD-14RT-6-HOLL	12-10 UNINSULATED SEAMLESS

Quick Connects	
AI-50177N	22-18 NYLON INSULATED
AI-50181N	16-14 NYLON INSULATED
AI-50186N	12-10 NYLON INSULATED
AI-50197N	22-18 NYLON INSULATED
AI-50198N	16-14 NYLON INSULATED
AI-50208	16-14 FULLY NYLON INSULATED
AI-50212	12-10 FULLY NYLON INSULATED
BU-190040001	22-18 FULLY INSULATED NYLON
BU-190040005	16-14 FULLY INSULATED NYLON
BU-190230003	22-18 VINYL INSULATED
BU-190230008	12-10 VINYL INSULATED
BU-190230010	16-14 VINYL INSULATED
BU-190230012	16-14 VINYL INSULATED

Spade Terminals	
AI-50050N	22-18 NYLON INSULATED #6 SPADE
AI-50060N	22-18 NYLON INSULATED #8 SPADE
AI-50070N	22-18 NYLON INSUL. #10 SPADE
AI-50140N	16-14 NYLON INSULATED #6 SPADE
AI-50150N	16-14 NYLON INSULATED #8 SPADE
AI-50160N	16-14 NYLON INSULATED
AI-50270N	12-10 NYLON INSULATED #6 SPADE
AI-50280N	12-10 NYLON INSULATED #8 SPADE
AI-50290N	12-10 NYLON INSULATED #10 SPADE
BU-191420003	22-18 VINYL INSULATED #6 SPADE
BU-191420005	22-18 VINYL INSULATED #8 SPADE
BU-191420007	22-18 VINYL INSULATED #10 SPADE
BU-191440015	16-14 VINYL INSULATED #6 SPADE
BU-191440020	16-14 VINYL INSULATED #8 SPADE
BU-191440026	16-14 VINYL INSULATED #10 SPADE
BU-191440037	12-10 VINYL INSULATED #6 SPADE
BU-191440039	12-10 VINYL INSULATED #8 SPADE
BU-191440042	12-10 VINYL INSULATED #10 SPADE