

RT3MP

3 pole male TINY xlr receptacle



Article Variations

Article Name	Details	Packaging
RT3MP	Nickel plated housing, gold plated contacts, max. panel thickness: 6 mm	Plastic Bag
RT3MP-D	Nickel plated housing, gold plated contacts, max. panel thickness: 6 mm	BULK

Technical Information

Product

Title	RT3MP
Connection Type	XLR

Electrical

Contact Resistance	$\leq 10 \text{ m}\Omega$
Insulation Resistance	$> 1 \text{ G}\Omega$
Dielectric Strength	$> 500 \text{ V rms}$
Rated current per contact	$< 5 \text{ A}$

Mechanical

Lifetime	>1000 Mating Cycles
Wiresize	0.22 mm ²
Wiresize	24 AWG

Material

Housing	Zinc
Washer	Steel
Nut	Brass
Plastic Body	PA66+30%GF
Pin	Brass
Housing	Nickel Plating
Washer	Nickel Plating
Nut	Nickel Plating
Pin	Gold Plating