



1. THIS CABLE TO BE MANUFACTURED IN COMPLIANCE WITH THE LATEST EC DIRECTIVE.
2. MARK EACH LABEL WITH SIGNAL NAME SHOWN IN CABLE CONNECTOR TABLE.
3. CABLE TO BE 3 CONDUCTORS, 18 AWG, UL 2517 RATED, 300V.
4. MARK LABEL PER CABLE LENGTH TABLE.
5. CABLE RATED AT 10A OR LESS.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE ECO 7675	7/25/17	J.KORDIK



4	CABLE LENGTH TABLE FINISHED LENGTH $\pm$ 2% TOTAL <table> <tr> <th data-bbox="107 1157 302 1174">MARK PART NO REV</th><th data-bbox="302 1157 472 1174">'L'</th></tr> <tr> <td data-bbox="107 1174 302 1190">3004-355-1M A</td><td data-bbox="302 1174 472 1190">1M (3.3 FT)</td></tr> <tr> <td data-bbox="107 1190 302 1205">3004-355-3M A</td><td data-bbox="302 1190 472 1205">3M (9.8 FT)</td></tr> <tr> <td data-bbox="107 1205 302 1221">3004-355-5M A</td><td data-bbox="302 1205 472 1221">5M (16.4 FT)</td></tr> <tr> <td data-bbox="107 1221 302 1237">3004-355-10M A</td><td data-bbox="302 1221 472 1237">10M (32.8 FT)</td></tr> </table>		MARK PART NO REV	'L'	3004-355-1M A	1M (3.3 FT)	3004-355-3M A	3M (9.8 FT)	3004-355-5M A	5M (16.4 FT)	3004-355-10M A	10M (32.8 FT)
MARK PART NO REV	'L'											
3004-355-1M A	1M (3.3 FT)											
3004-355-3M A	3M (9.8 FT)											
3004-355-5M A	5M (16.4 FT)											
3004-355-10M A	10M (32.8 FT)											

CABLE/CONNECTOR TABLE		
PIN NO	LEAD COLOR	SIGNAL
1	RED	U
2	YELLOW	V
3	BLUE	W
DRAIN	YELLOW/GREEN	SHI D/GND

8	2	FIT 221-3/8-BLK	SHRINK TUBING, DIA 3/8 IN, LENGTH AS NEEDED	ALLIED
7	-	-	-	-
6	4	LAT-15-361-1	LABEL, IDENTIFICATION, SMALL	BRADY OR EQUIVALENT
5	1	LAT-27-361	LABEL, IDENTIFICATION	BRADY OR EQUIVALENT
4	4	350536-1	CONTACT, CRIMP	AMP OR EQUIVALENT
3	5	E1006	TERMINAL, WIRE END	KST
2	1	350780-1	CONN., 4 POS	AMP OR EQUIVALENT
1	1		CABLE, 3 CONDUCTOR (AS SHIPPED)	
ITEM NO.	QTY REQD	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION	MFG.
TOLERANCES			THIRD ANGLE PROJECTION	 APPLIED MOTION PRODUCTS, INC.
DECIMALS: MM (INCH) X.XXX = ±0.013 (.005) X.XX = ±0.25 (.01) X.X = ±2.5 (0.1) ANGLES: MACH. = ±.5° CHAM. = ±5°				
COMPUTER DATA BASE DRAWING			APPROVALS	DATE
			DRAWN R.JONEZ	7/18/17
			CHECKED	
			APPROVED	
			SCALE: NONE	SHEET 1 OF 1
			POWER CABLE, STD, 10A, SV200DC SERVO DRIVES	
			B	DWG NO. 3004-355-XXX
			REV A	