
_								
Ī	CONNECTION CHART - MULTI-USE							
	J1 PIN	J2 PIN	RS-485	CANOpen				
Ī	1	1	RX+	N/C				
I	2	2	RX-	N/C				
	3	3	TX+	GND				
	4	4	TX-	CAN-H				
ſ	5	5	GND	CAN-L				

	REVISIONS						
ECO	REV	DESCRIPTION	DATE	APPROVED			
7962	Α	INITIAL RELEASE	5/29/18	J KORDIK			





VIEW A-A PIN NUMBERS A-CODED, FEMALE VIEWED FROM END



VIEW B-B PIN NUMBERS A-CODED, MALE VIEWED FROM END

CABLE LENGTH TABLE FINISHED LENGTH ± 2% TOTAL					
MARK PART NO REV	, _				
3004-384-1M A	1M (3.28 FT)				
3004-384-3M A	3M (9.84 FT)				
3004-384-5M A	5M (16.4 FT)				

NOTES: UNLESS OTHERWISE SPECIFIED

- 1. THIS CABLE IS MANUFACTURED IN COMPLIANCE WITH THE CURRENT EU RoHS DIRECTIVE.
- 2. REFER TO CONNECTION CHART FOR ASSOCIATED CONNECTOR PINS.

TOLERANCES	THIRD ANGLE PROJECTION		APPLIED MOTION PRODUCTS, INC.		
DECIMALS: MM (INCH) X.XXX= ±0.013(.005)					
$X.XX = \pm 0.25 (.01)$	\Box	7	COMMUNICATION CAI		TION CABLE
$X.X = \pm 2.5$ (0.1) ANGLES:	APPROVALS	DATE	STRAIGHT DAISY CHAIN RS-485/CANOpen		
MACH. = ±.5°	DRAWN R.JONEZ	5/11/18			
	CHECKED	5, 11, 15	D DWG NO.	REV	
0.1.1.1.1.	OFFICINED		ט	3004	-384-XXX A
	APPROVED		SCALE:	NTS	SHEET 1 OF 1