



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	WATTAGE	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
OP2105	6.0	2.0	12.00	100	100	FC-6U

\*LAMP RATED ONLY WITHOUT BASE.

<b>METRIC</b>  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
	DRAWN BY L. WENGSTROM		APPV'D BY J.K.		DATE 3/26/01	
SIZE <b>A</b>		FSCM NO. <b>55335</b>		DRAWING NO. <b>OP2105</b>		
TITLE <b>Single Contact Bayonet Lamp 6V 12W BA15s/19 Base</b>		SCALE <b>NONE</b>		RELEASED DATE <b>3/26/01</b>	REVISION DATE	
REV. NO.		DESCRIPTION/ECO NUMBER		APPV'D DATE	REV. NO.	
RELEASED AS CAD		3/26/01		SHEET <b>1 OF 1</b>		