



Type

# Clamp-type Test Probe 2 mm system



## KLEPS 2

Miniature clamp-type test probe with solder connection. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Remove actuator button for soldering, when cable is connected, press back on until it engages.

Clamping range  
Clamp type

2 mm  
contact hook

PART NO. / Housing color

931467100 ●  
931467101 ●



## KLEPS 2 BU

Miniature clamp-type test probe with 2 mm diameter socket connection. Gold-plated sprung copper beryllium contact spring. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Suitable for connection to wire-wrap posts up to a maximum of 1 x 1 mm.

2 mm  
contact hook

973501100 ●  
973501101 ●

### Technical data

Type of termination  
Rated voltage  
Measurment cat. acc. to IEC61010  
Rated current\*

Solder Terminal  
30 VAC / 60 VDC  
CAT I  
6 A

Contact resistance

15 mOhm

### Material Specifications

Contact material

contact hook: spring bronze

Contact surface material

gold

Housing material

PA

### Environmental conditions

Temperature range

-25 °C to +100 °C

### Inflamability class

Housing (basic material)

UL 94 V-2

spring-loaded socket Ø 2 mm  
30 VAC / 60 VDC  
CAT I  
6 A  
15 mOhm

contact hook: bronze,  
contact spring: copper beryllium

gold

PA

-25 °C to +100 °C

UL 94 V-2

### Drawing

Measurements are shown in millimeters.  
Multiply by 0.03937 to convert to inches.

