

Contactor

3 Pole / Frame Size 400AF



Altech Corp.®

includes 2 x AU-100-11
Auxiliary switch,
(2NO/2NC)

Additional Auxiliaries
and other accessories
see page 11-13

400AF

Type	MC-265A	MC-330A	MC-400A
Number of Poles	3	3	3
NEMA Size	5	5	5
Standard Auxiliaries	2NO/2NC	2NO/2NC	2NO/2NC

	Coil Voltage		Part. No.	Part. No.	Part. No.
AC/DC Common Coil	AC 50/60Hz	DC			
	100-240V	100-220V	MC-265A-100/200V	MC-330A-100/200V	MC-400A-100/200V
	265-347V	–	MC-265A-300V	MC-330A-300V	MC-400A-300V
	380-450V	–	MC-265A-400V	MC-330A-400V	MC-400A-400V
	440-575V	–	MC-265A-500V	MC-330A-500V	MC-400A-500V

HP Rating / UL508

		HP	HP	HP
	Continuous current	300A	350A	450A
Single phase	110~120V	–	–	–
	220~240V	–	–	–
Three phase	200~208V	75	100	125
	220~240V	100	125	150
	440~480V	200	250	300
	550~600V	200	250	300

Overload Relays

(Class 10A,
Differential Typical)



MT-400

Setting Ranges (A)

85-125A
100-160A
120-185A
160-240A
200-330A
260-400A

Frame Size 400AF

MT-400/3K-125
MT-400/3K-160
MT-400/3K-185
MT-400/3K-240
MT-400/3K-330
MT-400/3K-400

Lug Terminals



Part. No.

AJ-220
AJ-400
AJ-800

Frame Size

225AF
400AF
800AF

Contactor 3 Pole

Drawings and other technical information can be found on page 14-20.