

630.113.103.923.000


ODU-MAC® Blue-Line

Socket insulation body 3-pos.




General information

Part number	630.113.103.923.000
Size	
Weight	5,6 g
customs tariff numbers	85469010



Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.



The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	3
Contact type	Sockets

Technical information

Max. creepage and air clearance distance	16.3 mm (creepage); 16.3 mm (clearance)
--	---

The current load information is valid for single contacts or fully equipped modules. For use in connector systems, the load should be reduced according to VDE 0298-4:2013-06

Mechanical and environmental data

Operating temperature	-40 °C – 125 °C
Mating cycles	10000

Material and surface treatments

Housing	Thermoplastic
---------	---------------

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.