

Not available anymore - alternative: G4 in size 1

Basic information

Part number	GE1M07-P04LJG0-0000
Category	Connector

Contact insert description

Number of contacts	4
Contact type	Sockets
Termination type	Solder cup
Termination diameter	0.85 mm

Technical information

Max. current single contact	7.5 A
-----------------------------	-------

Mechanical and environmental data

Mating cycles	5.000
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	5.99 g

Material and surface treatments

Insulator material	PEEK
Contact material	Gold

Further technical information and downloads

[3D-File \(STP File\)](#)