

S20LAC-P10BMM9-320S
series_l
type_s2



General information

Part number	S20LAC-P10BMM9-320S
Termination	solder
Size	0
Locking principle	push
Coding	a_key
Cable Diameter	cable_mini_32
Cable outlet	bend_relief



Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.

CODING: 30 °

POSITIONS: 10 Positions

DIMENSIONS

The pin layout corresponds to the view on the termination area

Contact insert description

Number of contacts	10
Contact type	pins
Contact diameter	4_05_6_03mm
Insulator material	peek
Wire cross section	24_awg_28_awg
Termination	solder
Termination diameter	07mm045mm
Data transmission	usb_32

reverse_gender_on_request

Connection diagram

con2_usb_32

Technical information

Max. creepage and air clearance distance	03_mm	06_mm
Nominal current single contact	05_a	iec_60512_5_2
Nominal current insert	2,75 A	vde_0298_4
Test voltage	06_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
data_text
ul_text
illustrative_text