






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER EO PI9555	7-11-07		RDR
	D	REVISED PER PCN E-20-009639	10JUL2020	DM	IG
	DI	REVISED PER PCN-25-234736	06FEB2025	GB	DM



SECTION A-A
CONDUCTOR WINGS

SECTION B-B
INSULATION WINGS

TE INTERNAL PN	DEUTSCH PN	REV	PLATING
1062-12-0144	1062-12-0144	G	Selective Au, Ni/Cu overall, Sn/Ni/Cu Wire Barrel
1062-12-0166	1062-12-0166	G	Selective Ni, Ni/Cu overall, Sn/Ni/Cu Wire Barrel

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.MEYER	14NOV2000	 TE Connectivity					
		CHK B.BYFORD	11JUL2007						
DIMENSIONS: INCH [mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R.REED	11JUL2007	NAME SOCKET, STAMPED CONTACT SIZE 12 12-14 AWG, .113-.176 INS					
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±	PRODUCT SPEC 108-151000							
		APPLICATION SPEC 114-151002		SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-1062-12-01XX	RESTRICTED TO -		
MATERIAL 	FINISH SEE TABLE	WEIGHT 1.0 g		CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV D1