






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER E.O. P20392	03DEC2009		RDR
	F	REVISED PER PCN :E-18-007949	23MAY2018	DD	DM
	F1	REVISED PER PCN-24-200133	18MAR2024	RK	CB
	F2	REVISED PER PCN-25-234736	06FEB2025	GB	DM



SECTION A-A
WIRE BARREL

SECTION B-B
INSULATION BARREL

TE INTERNAL PN	DEUTSCH PN	REV	PLATING
1062-20-0322	1062-20-0322	J	Ni/Cu Overall
1062-20-0344	1062-20-0344	J	Selective Au, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1062-20-0377	1062-20-0377	J	Sn/Ni/Cu Overall

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 02DEC2009		TE Connectivity				
DIMENSIONS: INCHES[mm]		CHK D. MEYER 02DEC2009						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±	APVD R. REED 03DEC2009		NAME SOCKET, SLEEVELESS, STAMPED CONTACT SIZE 20 16-22 AWG, .075-.125 INS				
		PRODUCT SPEC 108-151000						
		MATERIAL 	FINISH SEE TABLE	APPLICATION SPEC 114-151003		SIZE	CAGE CODE	DRAWING NO
WEIGHT 0.17 g				A3	4AFU8	Ⓒ-1062-20-03XX	-	
CUSTOMER DRAWING						SCALE 6:1	SHEET 1 OF 1	REV F2