



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	7	ECR-12-015027	24AUG2012	HD	CD
	A	REDRAWN IN CREO	16MAY2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

AS SUPPLIED		AS RECOVERED			
EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		TOTAL WALL THICKNESS AFTER RECOVERY (W)	
mm.	in.	mm.	in.	mm.	in.
9.50-12.00	0.374-0.472	1.50	0.059	1.60±0.20	0.063±0.008

PRODUCT INFORMATION


- NON-FLAME RETARDANT
- OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN COLOUR: CLEAR
INNER LINER: HOT MELT ADHESIVE COLOUR: LIGHT AMBER
- LONGITUDINAL SHRINKAGE ON FULL RECOVERY: -5 TO -15%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED
FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING
- SUPPLIED WALL THICKNESS CONCENTRICITY: 60% MINIMUM

STANDARD CUTTING TOLERANCES(mm)

CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED.

0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±

FINISH

-
-

DWN 16MAY2023

BASAVARAJA D A

CHK 16MAY2023

SELVAPANDIAN B

APVD 16MAY2023

MAYO BAKARE

PRODUCT SPEC

RK-6214

APPLICATION SPEC

-

WEIGHT 12.99g/m

CUSTOMER DRAWING



TE Connectivity

NAME
RPPM-NR510
DUAL WALL SLEEVING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - RPPM-NR510

SCALE NTS SHEET 1 OF 1 REV A