



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2138011-1
EVC135 RELAY, SPST-NO, DM

Customers Also Bought



TE Part #815678-SF
FN2210HV-600-99-R9



TE Part #813439-SF
FN2211HV-400-99-C27-R99



TE Part #1618002-1
EV200A1ANA=RELAY,UN-ECON
EV200



TE Part #1618387-3
LEV200A4ANA=RELAY, SPST-NO



TE Part #1703810-2
SLIDE,TAB HSG GROUP B



TE Part #2358664-2
FLAP, ASSY, INLET COMBO 2, LEFT




TE Part #2375502-2
CHARGE INLET, COMBO 2, 90
DEGREE



TE Part #2310540-1
HVA280 2P HEADER ASSY, KEY A



TE Part #5-2355198-2
HVP800 2P HEADER ASSY



TE Part #2380291-1
2P HVP800 HARNESS FOR HINO

Documents

Product Drawings

RELAY, EVC135, 26 OHM COIL (15" WIRE)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2138622-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2138622-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2138622-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Automotive Relay Application Notes

English

[High Voltage Relays & Contactors, EVC 135 Contactor](#)

English

[High Voltage Relays & Contactors, EVC 135 Contactor](#)

English

Product Specifications

Definitions General Purpose Relays

English