




Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #216604-7
2X 7P HV190FEDERLEI



TE Part #640445-4
04P MTA156 HDR ASSY FL/STR SN




TE Part #1-825437-0
MOD 2 PINHDR 1X10P.



TE Part #826632-3
3P AMPMODU II PIN HDR.




TE Part #6-1393243-8
RT424024



TE Part #2-1761608-3
IDC LOW PRO HDR 10P VERT SHT L




TE Part #9-1879338-4
CPF 0603 249K 1% 50PPM 1K RL



TE Part #9-2176307-5
RP 1E 0.1W 118K 0.1% 25PPM 5K RL



TE Part #5179029-1
0.8FH,P06H.5,040,08/Sn,TU



TE Part #2-2176316-7
MELF SMA_A 15K 0.1% 15PPM 0207 1W

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1393763-7_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1393763-7_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1393763-7_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Reed Relay V23100-V4

English

Product Specifications



Product Specification

English

Definitions General Purpose Relays

English