



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #CAT-T3437-Z1
Z-Type Push-On Markers



TE Part #AKA012N00410100000
623 EXTENSION, SPEEDTEC



TE Part #T1349160120-000
H16A-TGH-M20



TE Part #80645-000
LS809-51 Liquid Level Sensor



TE Part #6-2213766-9
AV19 DPL 3A POWER LED YELLOW 12V




TE Part #2-2364570-8
AVH19 FLT SS LK RNG R&B 24V16A



TE Part #1-2364686-5
AVH22 FLT SS MT RNG GRN 24V16A



TE Part #2842104-8
8P,2MM,BRK HDR,SRVT,SMD,0.76AU, TR W/CAP



TE Part #1-281786-2
PLUG HE14 IDC 180 12 P AWG 28-26

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1393818-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1393818-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1393818-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Definitions General Purpose Relays

English

