

8241



70/30 Isopropyl Alcohol

This product contains 70% isopropyl alcohol, packaged in a convenient spray bottle for cleaning electronics. It effectively cleans ionic, polar and non-polar residues. It is safe on most painted surfaces, plastics, and elastomers. It leaves no residue and evaporates quickly relative to water. It is low toxicity compared to alternative solvents and is similarly relatively environmentally benign, being ozone safe with excellent “green solvent” scores.

This product is packaged in a spray bottle; however, it is also offered in presaturated wipe format. Additionally, we offer liquid 99.9% IPA and 99.9% IPA presaturated wipes.

Features & Benefits

Saturated with 70% IPA

Wipe size: 13 cm x 15 cm (5" x 6")

Wipe Density: 60 GSM

Lint-free and tear resistant

Safe on plastics

CARB compliant (category and limit: electronics cleaner, 75%)

Storage and Handling

Store between -20 and 27 °C in a dry area, away from sunlight.
Store in well-ventilated places (see SDS).

Properties

Color	Colorless
Odor	Alcohol
Evaporation Rate	1.5 (ButAc=1)
Density	0.87 g/mL
Flash Point	18 °C
Boiling Point	82 °C
Auto-ignition Temperature	425 °C
Volatile Organic Compound (VOC)	70%
Shelf Life	5 y



Available Packaging

Part #	Packaging	Net Vol.	Net Wt.
8241-475ML	Spray Bottle	475 mL	407 g
8241-475MLCA	Spray Bottle	475 mL	407 g
8241-945ML	Bottle	945 mL	811 g
8241-945MLCA	Bottle	945 mL	811 g
8241-945MLX6	6 Bottles	5.67 L	4.6 kg
8241-945MLCAX6	Bottles	5.67 L	4.6 kg

Disclaimer: This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.