







RECOMMENDED PANEL CUTOUT

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
L-2	NONE	L-1



NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATING:
ANSI/UL 61058-1
16(8)A @ 125/250VAC T55 [cURus] [ENEC-15]
- CONTACT RESISTANCE: 20m Ω MAX. @ 50VAC INITIAL
- INSULATION RESISTANCE: 100M Ω MIN. @ 500VDC
- DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 10,000 CYCLES
- OPERATING TEMPERATURE: 0°C to 55°C
- INGRESS PROTECTION: IP67
- ILLUMINATION VOLTAGE: 125VAC
- ▲ DENOTES CRITICAL PARAMETER



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-102562	RELEASE	02/28/24	JS	TITLE RB343A1100-336				100126888
					SCALE	DATE	DR	DWG	REV
					1:1	2/22/2024	JS	14-RB343A1100336	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED