




() MOMENTARY



NOTE:

2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$

3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER

▲ 5. CONTACT RATING:

ANSI/UL 61058-1

16(8)A @ 125/250VAC T55 [cURus] [ENEC-15]

6. CONTACT RESISTANCE: 20mΩ MAX. @ 50VAC INITIAL

7. INSULATION RESISTANCE: 100MΩ MIN. @ 500VDC

8. DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE



9. ELECTRICAL LIFE: 10,000 CYCLES

10. OPERATING TEMPERATURE: 0°C to 55°C

11. INGRESS PROTECTION: IP67

▲12. ILLUMINATION VOLTAGE: 125VAC

13. ▲ DENOTES CRITICAL PARAMETER



OBJECT ID
100124001

TITLE	RB346A1100-136
-------	----------------

SCALE 1:1

DATE 3/28/2023

DR
JS

DWG	14-RB346A1100136
-----	------------------

REV
C