


MATERIAL: BRASS

PLATING: Au/Ni

WIRE SIZE: 20-26 AWG RECOMMENDED

CONTACT CURRENT RATING: 5A MAX.

NOTE #1: CONTACTS SUPPLIED
LOOSE PIECE (500 PER BAG)



ONCE INSERTED INTO NORCOMP 170 SERIES CRIMP AND POKE CONNECTORS,
CANNOT BE REMOVE.

	NORCOMP PART NUMBER
250 MATING CYCLES	170-202-170L003
30µin GOLD PLATING	170-202-170L005

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

DATE:
01/15/2009

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET 1 OF 1

REV
12

DWG NO. 170-202-170L00Y