

SPECIFICATIONS:

MATERIALS:





INSULATOR:	PA9T, UL94 V-0, BLACK
CONTACTS:	GOLD PLATED BRASS
RIVET:	NICKEL PLATED BRASS
SCREWLOCK:	NICKEL PLATED ZINC ALLOY
BOARDLOCK:	TIN PLATED STEEL
SHELL:	NICKEL PLATED STEEL

ELECTRICAL:


RATED CURRENT:	5A
DIELECTRIC WITHSTAND VOLTAGE:	1000VAC for 1 MIN.
INSULATION RESISTANCE:	1000 MOhms MIN.
CONTACT RESISTANCE:	15 mOhms MAX.

ENVIRONMENT:

OPERATING TEMPERATURE:	-55°C TO +105°C
------------------------	-----------------



No. OF PINS	DIMENSIONS		
	A	B	C
9	1.213	0.984	0.666
	30.81	24.99	16.92
15	1.541	1.312	0.994
	39.14	33.32	25.25
25	2.088	1.852	1.534
	53.04	47.04	38.96
37	2.729	2.500	2.181
	69.32	63.50	55.42



RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
04/28/2005

UNITS = inch [mm]

NorComp

DO NOT SCALE FROM DRAWING





SCALE:
NTS

SHEET 1 OF 2

REV 15

DWG NO.

183-YYY-113RYY1

	 0.141 ±0.020 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 0.500 METAL SHELL FORK BOARD LOCKS	 0.500 METAL SHELL FORK BOARD LOCKS
 0.120" DIA. HOLE	16	N/A	N/A	55
 4-40 FLUSH INSERT	17	45	57 BOARD LOCKS IN REAR HOLE (0.590")	53 BOARD LOCKS IN FRONT HOLE (0.590")
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	54 BOARD LOCKS IN REAR HOLE	56 BOARD LOCKS IN FRONT HOLE
 4-40 ROUND STANDOFF FEMALE SCREWLOCK	N/A	N/A	N/A	N/A

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
P. JENKINS

DATE:
04/28/2005

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:
NTS

SHEET OF
2 2

REV
15

DWG NO. 183-YYY-113RYY1